



MSD INC.

ENGINEERING DATA SHEET

RELAY TYPE: FCA-325-BZ4 | COMPUTER PART No.: 9383509 | TEST PROCEDURE
 CUSTOMER/SPECIFICATION: CATALOG ITEM | REV N/A | MSDP-791

TEST REQUIREMENTS

$\pm 10\%$
 COIL RES.: 290 OHMS OPERATE TIME: 15 mS MAX RELEASE TIME: 15 mS MAX
 CONTACT MAKE BOUNCE: 1.0 mS MAX N.O. BREAK BOUNCE: 0.1 mS MAX
 CONTACT STABILIZATION TIME: N/A RATED COIL VOLTAGE: 28Vdc
 CONTACT VOLTAGE DROP: MFG TEST: 0.5 mV @ 100mA - 6Vdc
 FINAL TEST: 60 mV @ 10A - 28Vdc
 HI-POT: 1250 Vrms ALL POINTS, EXCEPT 1000 Vrms COIL TO CASE
 INSULATION RESISTANCE: 100 MEGOHMS MIN @ 500 Vdc
 VIBRATION: N/A
 SEAL TEST: 1×10^{-8} MAX LEAK RATE COIL TRANSIENT SUPPRESSION: 42 Vdc MAX
 OTHER: _____



Prepared By: Date		Approved By: Date	
LES WYNNE 7-24-96			
Rev	ECN No.	Date	
A	96-065	7-24-96	

SPECIAL INSTRUCTIONS