





AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX		MILITARY P/N AND CLASS		QUANTITY	PACKAGE TYPE	PART NO
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		MS25036-150 CLASS 2		100	LOOSE PIECE, BOX	8-320571-1
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		MS25036-150 CLASS 1 & 2		5000	ON TAPE, REEL	2-320571-2
FOR ORDER ENTRY		1-800-526-5142		COPPER PER ASTM B-152 SLEEVE, RED NYLON		1000	LOOSE PIECE	320571
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN PLATE PER ASTM B545		NAME TERMINAL, RING TONGUE, PIDG™, WIRE SIZE: 22-16 AWG		
						SIZE B		
						CAGE CODE 00779		
						DRAWING NO C-320571		
						SHEET 1 OF 2		



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

FOR APPLICATION

TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER

1-800-522-6752

TOOLING ASSISTANCE CENTER

1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX

VOLTAGE RATING: 300 V MAX

WIRE RANGE: 22 20 18

CIRC MIL AREA: 0.38mm² [754] 0.60mm² [1,186] 0.96mm² [1,900]

STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MILITARY P/N AND CLASS

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -

MATERIAL COPPER PER ASTM B-152 SLEEVE, RED NYLON

FINISH TIN PLATE PER ASTM B545

WHITE

RED

GREEN

STRIPE COLOR

STAMPING

WIRE SIZE

QUANTITY

PACKAGE TYPE

PART NO

AMP

AMP Incorporated Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, I.R., PIDG™, WIRE SIZE: 22-16 AWG

SIZE

CAGE CODE

DRAWING NO

SCALE

NTS

SHEET

2 OF 2