

Professionally approved products.

Datasheet

Leak & Flaw Detector Spray

RS Stock number [388-8623](#)



Description:

A non-flammable water based foam for the visible detection of gas leaks from sealed installations.

For use on surfaces of pressurised installations where leakage is suspected.

Do NOT use on areas where phosphorous containing gases are involved.

Do NOT use in conjunction with gases likely to react or decompose in contact with moisture or water.



Professionally approved products.

Benefits:

Ease of use, virtually instant detection via visible bubble streams.
Non-flammable
Completely inert
Non-corrosive
Easily removed, completely water soluble

Physical Properties:

This is for the detector base unless otherwise stated.

Appearance:	A slightly hazy liquid with an ammoniacal odour
pH (10% Solution):	9 - 11
Specific Gravity:	1.000 ± 0.01
Non Volatiles % m/m:	2 - 10
Active Content % m/m, as supplied:	90 - 99
Viscosity:	Very slightly viscous
Flammability, as supplied:	Non-flammable
Composition Data, as supplied:	An aqueous solution of coconut ethanolamides and ammonium
Service Temperature (Continuous):	Designed for use at ambient temperatures.

Application Details:

Shake the can before use, and apply liberally, directly to the area of the suspected leak. Inspect the area for creation of a bubble stream.

Availability:

400 ml Aerosol