

# Geocel® JOINERS MATE

## 5 MINUTE RAPID WOOD ADHESIVE

**Geocel® Joiners Mate**, 5 minute rapid wood adhesive is a clear one part moisture curing wood adhesive, which sets in just 5 minutes. It is a thixotropic gel with exceptionally high bond strength, resistant to most chemicals, and 100% seawater proof.

- Versatile – sticks wood to many common construction substrates
- Maximum strength one part clear polyurethane
- For internal and external use
- Thixotropic – ideal for vertical joints
- Fast setting – reacts with moisture to set in just 5 minutes
- Weather proof
- Seawater proof
- Resistant to acid and chemicals
- Can be worked, shaped and painted

### SPECIFICATIONS

BSEN 204 Class D4



## TECHNICAL DATA

<b>Storage Life</b>	Approx 12 months when stored in a cool, frost free place. Less once cartridge has been opened
<b>Density</b>	1.12g/cm <sup>3</sup>
<b>Viscosity</b>	paste/thixotrope approx 100,000 MPa.s at 20°C
<b>Solids Content</b>	approx 100%
<b>Open Time</b>	approx 10 min
<b>Press Time</b>	30min at +15°C up to +20°C & 2hrs at +10°C
<b>Full Cure</b>	after 21hrs approx. 90% of ultimate strength
<b>Water Resistance</b>	class D4 (BSEN 204) applicable in internal spaces in which, frequently and during longer periods, condensation occurs and applicable in external spaces exposed to weather influences with an adequate protection of the glued wood
<b>Colour</b>	Clear
<b>Temperature Resistance</b>	-30°C up to +100°C
<b>Coverage</b>	approx. 250 to 400 g/m <sup>2</sup> depending on surface
<b>Application Temperature</b>	+5°C up to +35°C

Specification writers: These values are not intended for use in preparing specifications. Please contact your local **Geocel® Sales Representative** prior to writing specifications on this product.

## APPLICATION

Ensure surfaces to be bonded are clean, dust and grease free. One of the surfaces must be porous, abrade non-porous surfaces. To achieve maximum bond strength and assist cure, slightly moisten one surface with a damp cloth. Do not over wet. Remove nozzle and cut the tip of the cartridge taking care not to damage the thread. Replace nozzle and cut cleanly at an angle of 45 degrees. Apply using a standard sealant gun. Wearing gloves is recommended. Apply adhesive evenly to one surface; only apply between 5°C and 30°C. If necessary, cover large surfaces with a fine-toothed spreader. Assemble parts IMMEDIATELY and clamp for 5-10mins at 20°C, (longer at lower temperatures). After this time, the joint may be easily handled. Final and full bond strength will be achieved after 30 minutes.

NOTE: The product foams slightly on application to fill small gaps. Any excess foam/adhesive must be removed with acetone before the product sets, or with a sharp chisel once set.

## FINISHING & CLEAN UP

Tools and excess adhesive must be cleaned immediately with acetone.

Close properly after use and store in a cool, frost free place.

## LIMITATIONS

**Geocel® Joiners Mate** is unsuitable for polyethylene, polypropylene, Teflon or nylon.

## PACKAGING

**Geocel® Joiners Mate** is supplied in 310ml cartridges packed in boxes of 12.

## HEALTH AND SAFETY

Health and Safety data sheets available on request.

## TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and Safety information, contact **Geocel® Technical Service**.

**IMPORTANT NOTE** Whilst all reasonable care is taken in compiling technical data on the company's products, all recommendations regarding the use of such products are made without guarantee since the conditions of use are beyond the company's control. It is the customer's responsibility to satisfy themselves that each product is fit for the purpose for which they intend to use it

# Geocel®

Geocel Limited

Western Wood Way, Langage Science Park, Plympton, Plymouth, Devon, PL7 5BG

Tel: 01752 334350 Fax: 01752 202065 Email: [info@geocel.co.uk](mailto:info@geocel.co.uk)

[www.geocel.co.uk](http://www.geocel.co.uk)