



ESB 2 PF 240:

Mains connection box set for single-phase 240V TN systems with IP65 enclosure.

Premounted with DEHNguard modular surge arrestors (part no. 952 200) and Europa Components single-pole circuit breaker type C63A 10kA (part no. EUC163C).

- Ready-to-install equipment for use acc. to the lightning protection zones concept as required in BSEN 62305-4
- Premounted with DEHNguard M ... surge arrester
- Quick and easy installation as premounted with SPD arrangements
- Maximum discharge capacity (I_{max} 40 kA) due to powerful zinc oxide varistors
- High reliability due to "Thermo Dynamic Control" monitoring device
- Allows for easy replacing of protection modules due to module releasing button
- Single-pole automatic circuit breaker type C63 A
- Operating state/fault indication by mark in the inspection window
- Enclosure with transparent cover, degree of protection: IP 65

ESB 2 PF 240

SPD Features	:
SPD according to EN 61643-11	Type 2
SPD according to IEC 61643-1	Class II
Nominal a.c. voltage [U _N]	240 V
Power supply system	TN system
Max. continuous operating a.c. voltage [U _C]	275 V
Nominal discharge current (8/20 μs) [I _n]	20 kA
Max. discharge current (8/20 μs) [I _{max}]	40 kA
Voltage protection level [U _p]	≤ 1.25 kV
Voltage protection level for 5 kA [U _p]	≤ 1 kV
Response time [t _A]	≤ 25 ns
Max. mains-side overcurrent protection	125 A gL/gG
Short circuit withstand capability for max. mains-side overcurrent protection	50 kA _{rms}
Temporary overvoltage (TOV) [U _{TOV}]	335 V / 5 sec.
TOV characteristics	withstand
Operating state/Fault indication	green / red
Cross-sectional area (min.)	1.5 mm ² solid/flexible
Cross-sectional area (max.)	35 mm ² stranded/25 mm ² flexible
SPD material	red thermoplastic, UL 94 V-0
MAINS CONNECTION BOX Features	:
Enclosure material	ABS with Polycarbonate lid

Degree of protection acc. to EN 60529	IP 65
Cover type	Transparent cover
Colour of enclosure	grey
Number of cable entries	8 cable entries
Capacity	4 modules
Dimension	Height: 210 x Width: 125 x Depth 83mm
FUSE Features	:
Rated current / Characteristics	circuit breaker C 63 A 10kA
Number of poles	single-pole

Change in form and technology, with masses, weights and materials we reserve ourselves in the sense of the progress of the technology. The illustrations are noncommittal.