


LC CONN. MARK		LC CONN. MARK
A	↔	B
B	↔	A

NOTES:

- 1
- ATTENUATION $\leq$ 0.3 dB, MEASURED AT 850 nm OR 1300 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2
- RETURN LOSS $\geq$ 20 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
- 3
- TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4
- CABLE INFORMATION:
 - CORE DIAMETER: 50/125 μ m
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: ORANGE
 - OUTER JACKET MATERIAL: LSZH

△5 BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061310-Y	XY.0

2	BLANK LABEL				3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE				2
L	FOCAB 1.8MZ 50/125, ORANGE, LSZH				1
Qty	Description				Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland		
		CHK A. HENGELMOLEN 16OCT2009			
		APVD A. HENGELMOLEN 16OCT2009			
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	FIBER OPTIC LEAD 1.8MZ LC/DPX - LC/DPX MULTI MODE 50/125		
MATERIAL -		FINISH -	APPLICATION SPEC -	WEIGHT -	SIZE A2
				CAGE CODE 00779	DRAWING NO C=2061310
					RESTRICTED TO -