

Classic ECO A55

CLECO A55 230V 70W E27 SV1

0023136



Range features

- 1:1 replacement of Incandescent A55 lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps



PRODUCT OVERVIEW

Ordering number	0023136
Light colour	828 Homelight
Technology	Halogen
Energy class	D
Average life (Rated) (h)	2000
Lamp finish	Clear
Lamp shape	GLS A55
Dimmable	Yes
Cap/Base	E27
Type	Classic 'A' Shape
EAN code	5410288231365
CRI (Ra)	100
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	1190
Watt (Nominal) (W)	70
Equivalent watt (W)	92
Voltage (V)	230

Classic ECO A55

CLECO A55 230V 70W E27 SV1

0023136

DATA TABLE

General data

Ordering number	0023136
Technology	Halogen
Average life (Rated) (h)	2000
Average life (Nominal) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp finish	Clear
Lamp shape	GLS A55
Dimmable	Yes
Cap/Base	E27
Type	Classic 'A' Shape
EAN code	5410288231365
Long description	1:1 replacement of Incandescent A55 lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 1500hrs or 2000hrs - up to two times more average life compared to incandescent lamps
Product name	CLECO A55 230V 70W E27 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Classic ECO A55

CLECO A55 230V 70W E27 SV1

0023136

Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	1190
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	1190

Electrical data

kWh per 1000 hours burning time	70
Watt (Rated) (W)	70
Watt (Nominal) (W)	70
Equivalent watt (W)	92
Voltage (V)	230
Lamp power factor	1

Physical data

Weight (kg)	0.03
Lamp Length (mm) - C/L	100
Max. Lamp Diameter (mm) - D	56
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	9.60 x 5.50 x 5.50
Inner package dimensions (L x W x H) (cm)	28.00 x 11.00 x 10.00
Inner package net weight (kg)	0.28
Outer package dimensions (L x W x H) (cm)	59.00 x 30.50 x 22.50


Classic ECO A55

CLECO A55 230V 70W E27 SV1


0023136

TECHNICAL DRAWINGS

Classic ECO A55



E27



ENERGY LABEL

