




10 9 8 7 6 5 4 3 2 1



ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PA	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	WIRES	COPPER/PVC	NONE
5	O-RING	NBR	BLACK
6	POTTING MATERIAL	EPOXY	NONE

COLOR CODE:

- 1 BROWN
- 2 WHITE
- 3 BLUE
- 4 BLACK



POL	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
4	1200845103	WR4J26E03C3003	300 ±10

VOLTAGE RATING: 250 VAC / VDC
AMPERAGE RATING: 4 A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0298 DRWN:NSTAUDIGEL 2010/01/28 CHKD: 2010/02/01 APPR:FPACHER 2010/02/02	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY NSTAUDIGEL	DATE 2010/01/28	TITLE RECEPTACLE MALE M12 -4P UL FRONT, PG9		
			4 PLACES	± ---	± ---	CHECKED BY				DATE
			3 PLACES	± ---	± ---					
			2 PLACES	± 0.05	± ---					
1	REV		1 PLACE	± 0.1	± ---	APPROVED BY FPACHER	DATE 2010/02/01	 MOLEX INCORPORATED		
			ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO. SD-120084-023		SHEET NO. 1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				