

1.0 SCOPE

This specification documents the detailed requirements for Analog Devices space qualified die including die qualification as described for Class K in MIL-PRF-38534, Appendix C, Table C-II except as modified herein.

The manufacturing flow described in the STANDARD DIE PRODUCTS PROGRAM brochure at <http://www.analog.com/aerospace> is to be considered a part of this specification.

This data sheet specifically details the space grade version of this product. A more detailed operational description and a complete data sheet for commercial product grades can be found at www.analog.com/MAT03

2.0 Part Number. The complete part number(s) of this specification follow:


Part Number	Description
MAT03-000C	Low-Noise Matched Dual PNP Transistor

3.0 Die Information

3.1 Die Dimensions

Die Size	Die Thickness	Bond Pad Metalization
70 mil x 60 mil	19 mil $\pm$ 2 mil	Al/Cu

3.2 Die Picture



1. C1
2. B1
3. E1
4. C2
5. B2
6. E2

Substrate can be connected to V- or floated.

ASD0012816

Rev.G

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 www.analog.com
Fax: 781.326.8703 © 2011 Analog Devices, Inc. All rights reserved.

3.3 Absolute Maximum Ratings ^{1/}

Collector to Base Voltage (BV _{CBO})	36V
Collector to Emitter Voltage (BV _{CEO})	36V
Collector to Collector Voltage (BV _{CC})	36V
Emitter to Emitter Voltage (BV _{EE})	36V
Collector Current (I _C)	20mA
Emitter Current (I _E)	20mA
Junction Temperature (T _J)	+150°C
Ambient Operating Temperature Range	-55°C to +125°C
Storage Temperature Range	-65°C to +150°C

Absolute Maximum Ratings Notes:

- ^{1/} Stresses above the absolute maximum rating may cause permanent damage to the device. Extended operation at the maximum levels may degrade performance and affect reliability.

4.0 Die Qualification

In accordance with class-K version of MIL-PRF-38534, Appendix C, Table C-II, except as modified herein.

- (a) Qual Sample Size and Qual Acceptance Criteria – 25/2
- (b) Qual Sample Package – 6 Lead Can Package (TO)
- (c) Pre-screen electrical test over temperature performed post-assembly prior to die qualification.

Table I - Dice Electrical Characteristics

Parameter	Symbol	Conditions ^{1/}	Limit Min	Limit Max	Units
Current Gain	h _{FE}	I _C = 1mA; V _{CB} = 0V, -36V	100		
		I _C = 100μA, V _{CB} = 0V, -36V	90		
		I _C = 10μA; V _{CB} = 0V, -36V	80		
Current Gain Match ^{2/}	•h _{FE}	I _C = 100μA; V _{CB} = 0V		3	%
Offset Voltage	V _{OS}	V _{CB} = 0V		100	μV
Offset Voltage Change vs. V _{CB}	•V _{OS} / •V _{CB}	V _{CB} = 0V, -36V		150	μV
Offset Voltage Change vs. Collector Current	•V _{OS} / •I _C	I _{C1} = 10μA, I _{C2} = 1mA, V _{CB} = 0V		50	μV
Input Offset Current	I _{OS}	V _{CB} = 0V, I _C = 100μA		35	nA
Bulk Emitter Resistance	r _{BE}			0.75	Ω
Collector Base Leakage Current	I _{CBO}	V _{CB} = -36V		200	pA
Collector Saturation Voltage	V _{CE} SAT	I _C = 1mA, I _B = 100μA		0.1	V

Table I Notes:

^{1/} V_{CB} = -15V, I_C = 10μA, T_A = 25°C, unless otherwise specified.

^{2/} Current gain match (□h_{FE}) is defined as: $\square h_{FE} = \frac{100(\Delta I_B) h_{FE \min}}{I_C}$.

Table II - Electrical Characteristics for Qual Samples

Parameter	Symbol	Conditions <u>1/</u>	Sub-groups	Limit Min	Limit Max	Units
Current Gain	h_{FE}	$I_C = 1\text{mA}; V_{CB} = 0\text{V}, -36\text{V}$	1	90		
			2, 3	60		
		$I_C = 100\mu\text{A}, V_{CB} = 0\text{V}, -36\text{V}$	1	80		
		$I_C = 100\mu\text{A}, V_{CB} = -36\text{V}$	2, 3	50		
		$I_C = 10\mu\text{A}; V_{CB} = 0\text{V}, -36\text{V}$	1	70		
		$I_C = 10\mu\text{A}; V_{CB} = -36\text{V}$	2, 3	40		
Current Gain Match <u>2/</u>	Δh_{FE}	$I_C = 100\mu\text{A}; V_{CB} = 0\text{V}$	1		3	%
Offset Voltage	V_{OS}	$V_{CB} = 0\text{V}$	1		120	μV
			2, 3		180	
Change in Offset Voltage vs. Temperature <u>3/</u>	TCV_{OS}	$V_{CB} = 0\text{V}$			0.5	$\mu\text{V}/^\circ\text{C}$
Offset Voltage Change vs. V_{CB}	$\bullet V_{OS} / \bullet V_{CB}$	$V_{CB} = 0\text{V}, -36\text{V}$	1		170	μV
Offset Voltage Change vs. Collector Current	$\bullet V_{OS} / \bullet I_C$	$I_{C1} = 10\mu\text{A}, I_{C2} = 1\text{mA}, V_{CB} = 0\text{V}$	1		70	μV
Input Offset Current	I_{OS}	$V_{CB} = 0\text{V}, I_C = 100\mu\text{A}$	1		55	nA
Bulk Emitter Resistance	r_{BE}		1		0.9	Ω
Collector Base Leakage Current	I_{CBO}	$V_{CB} = -36\text{V}$	1		250	pA
Collector Saturation Voltage	$V_{CE\text{SAT}}$	$I_C = 1\text{mA}, I_B = 100\mu\text{A}$	1		0.1	V
Breakdown Voltage	BV_{CEO}		1	36		V

Table II Notes:

1/ $V_{CB} = -15\text{V}, I_C = 10\mu\text{A}$, unless otherwise specified.2/ Current gain match ($\square h_{FE}$) is defined as: $\square h_{FE} = \frac{100(\Delta I_B)h_{FE\text{min}}}{I_C}$.3/ Guaranteed by V_{OS} test $\left(TCV_{OS} \cong \frac{V_{OS}}{T} \text{ for } V_{OS} \ll V_{BE} \right)$ $T = 298^\circ\text{K}$ for $T_A = +25^\circ\text{C}$.

Table III - Life Test Endpoint and Delta Parameter (Product is tested in accordance with Table II with the following exceptions)								
Parameter	Symbol	Sub-groups	Post Burn In Limit		Post Life Test Limit		Life Test Delta	Units
			Min	Max	Min	Max		
Current Gain @ 1mA	h_{FE}	1	90		80		± 40	
		2, 3			50			
Current Gain @ 100••	h_{FE}	1	80		70		± 36	
		2, 3			40			
Current Gain @ 10••	h_{FE}	1	70		60		± 32	
		2, 3			30			
Input Offset Current	I_{OS}	1		55		75	± 20	nA
		2, 3						

5.0 Life Test/Burn-In Information

- 5.1 HTRB is not applicable for this drawing.
- 5.2 Burn-in is per MIL-STD-883 Method 1015 test condition A, B, or C.
- 5.3 Steady state life test is per MIL-STD-883 Method 1005.

Rev	Description of Change	Date
A	Initiate	Feb. 28, 2002
B	Update web address. Change ΔhFE condition on table II from 10uA to 100uA.	Aug. 11, 2003
C	Edit pqualib ecn rev history to add "Change ΔhFE condition on table II from 10uA to 100uA."	Oct. 20, 2003
D	Update header/footer and add to 1.0 Scope description.	Feb. 29, 2008
E	Add Junction Temperature & Ambient Operating Temperature Range to section 3.3-Absolute Maximum Ratings.	April 3, 2008
F	Updated Section 4.0c note to indicated pre-screen temp testing being performed.	June 5 2009
G	Updated fonts and sizes to ADI standards	Oct. 7, 2011

