

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

DEC ,2005.

© COPYRIGHT 2005 By --

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		D	ECR-15-002281	12FEB2015	RZ	MC

NOTES:

⚠ PACKAGE ONE COMPLETE CONNECTOR IN HEAT SEALED, LABELED BAG/ 250 PER SHIPPING BOX. LABELED PER TEC-107-115

⚠ 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275

⚠ Ag PLATING

4 ELECTRICAL CHARACTERISTICS


FREQUENCY RANGE:	DC - 4 GHz
NOMINAL IMPEDANCE:	50 Ohm
INSULATION RESISTANCE:	5000 MOhm
WORKING VOLTAGE:	500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE:	1500 Volts RMS Max
CONTACT RESISTANCE:	
CENTER CONTACT:	1.50 mOhm Max
OUTER CONTACT:	1.00 mOhm Max
VSWR @ 3GHz:	1.35 Max
INSERTION LOSS xdb:	N/A

5 MECHANICAL CHARACTERISTICS


COUPLING RETENTION FORCE:	N/A
CABLE RETENTION FORCE:	N/A
MOUNT NUT RECOMMENDED TORQUE:	2.5 Nm
DURABILITY:	500 Cycles Min

6 ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:	-65 to +165 DegC
------------------------	------------------



RECOMMENDED MOUNTING HOLE



NOT RELEASED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 13DEC05	TE TE Connectivity		
		CHK S.PARLOW 13DEC05			
		APVD F.WHEELER-KING 13DEC05			
		PRODUCT SPEC --			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME BNC BULKHEAD SOCKET FRONT MOUNT 50 OHM + TAG --	
		0 PLC ± --		SIZE A3	
		1 PLC ± 0.2		CAGE CODE 00779	
		2 PLC ± --		DRAWING NO C-1337450	
		3 PLC ± --		RESTRICTED TO --	
4 PLC ± --		APPLICATION SPEC --		SCALE NTS	
4 ANGLES ± --		WEIGHT --		SHEET 1 OF 1	
MATERIAL SEE TABLE		FINISH --		REV D	
		CUSTOMER DRAWING			