


VCT.FP

Lobe knobs



ELESA Original design



Elesa Standards		Main dimensions					Mounting hole		Weight
Code	Description	D	L	d ₁	d ₃	l ₂	d _{6H}	h	g
69847	VCT.32 FP-M5	32	23	15	10	10	M5	12	11
69848	VCT.32 FP-M6	32	23	15	10	10	M6	12	10
69849	VCT.32 FP-M8	32	23	15	10	10	M8	12	9
69897	VCT.40 FP-M6	40	27	17	12	12	M6	18	26
69898	VCT.40 FP-M8	40	27	17	12	12	M8	18	24
69899	VCT.40 FP-M10	40	27	17	12	12	M10	17	23
69956	VCT.50 FP-M8	50	32	19	15	14	M8	20	38
69957	VCT.50 FP-M10	50	32	19	15	14	M10	20	34
69958	VCT.50 FP-M12	50	32	19	15	14	M12	20	30
70016	VCT.63 FP-M8	63	37	22	19	16	M8	26	44
70017	VCT.63 FP-M10	63	37	22	19	16	M10	26	42
70018	VCT.63 FP-M12	63	37	22	19	16	M12	26	40
70067	VCT.74 FP-M12	74	43.5	26	17	22	M12	26	56
70068	VCT.74 FP-M14	74	43.5	26	17	22	M14	26	52
70069	VCT.74 FP-M16	74	43.5	26	17	22	M16	31	54



* Complete with colour index, example: CA.VCT.40-C2

C9
RAL9005
 C2
RAL2004
 C3
RAL7035
 C4
RAL1021
 C5
RAL5024
 C6
RAL3000

C9	C2	C3	C4	C5	C6		Cap for
Code						Description	
6900	6903	6904	6905	6906	6901	CA.VCT.32-*	VCT.32
6910	6913	6914	6915	6916	6911	CA.VCT.40-*	VCT.40
6920	6923	6924	6925	6926	6921	CA.VCT.50-*	VCT.50
6930	6933	6934	6935	6936	6931	CA.VCT.63-74-95-*	VCT.63-74-95

Material

High resilience polypropylene based (PP) technopolymer. Resistant to solvents, oils, greases and other chemical agents.

Colour

Black, matte finish.

Standard execution

Brass boss, threaded pass-through hole.

Accessories on request

Coloured centre caps (see table).



STANDARD MACHINE ELEMENTS WORLDWIDE

ELESA models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings.