

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19160-0070](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 14-22 AWG Wire, Tape and Reel

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-015 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Splices](#)
 Product Name Closed-End Insulated
 UPC 800753110762

Physical

Barrel Type Closed
 Color - Resin Natural
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.462/g
 Packaging Type Adhesive Tape on Reel
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 6.10mm max.
 Wire Size AWG 14, 16, 18, 20, 22
 Wire Size mm² 0.25 - 2.60

Electrical


Voltage - Maximum 300V

Material Info

Old Part Number NC-2214T

Reference - Drawing Numbers

Packaging Specification PK-19408-109
 Product Specification PS-19902-015
 Sales Drawing SD-19160-001



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No**
**Low-Halogen Status
 Low-Halogen**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

19160Series

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880242

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION