

---

## PT-FIT 70/220...240 I

POWERTRONIC PT-FIT I | ECG for HID lamps, with cable clamp



---

### Areas of application

- Shop lighting
- Health and fitness areas (in dry, corrosion-protected place)
- Effect and accent lighting

---

### Product benefits

- ECG with ergonomic strain relief for correct installation in suspended ceilings
- Optimized cost/benefit factor
- Automatic safety shutdown of lamps in the event of a defect or at end of life (EoL)

---

### Product features

- Energy Efficiency Index EEI: A2
- Supply voltage: 220...240 V
- Line frequency: 50...60 Hz
- RI suppression: to EN 55015/CISPR 15
- Safety: to EN 61347-2-12
- Line harmonics according to EN 61000-3-2
- Immunity according to EN 61547

Technical data

Electrical data

Lamp wattage	73 W
Line current	0.36 A <sup>1)</sup>
Ignition voltage	4.5 kVp
Operating frequency	0.200...0.240 kHz
System wattage	80.00 W
ECG efficiency	92 %
Input voltage AC	220...240 V
Input voltage range	198...264 V
Mains frequency	50...60 Hz
Power factor $\lambda$	0.95 <sup>2)</sup>
Inrush current	45 A <sup>3)</sup>
Max. no. of ECGs on circuit breaker 10 A	7 <sup>4)</sup>
Max. no. of ECGs on circuit breaker 16 A	13 <sup>4)</sup>
Max. no. of ECGs on 16A MCB with EBN-OS	32 <sup>4)</sup>
Protective conductor current	0.3 mA
U-OUT (working voltage)	250 V
Max. working voltage between LH and LL	250 V
Max. working voltage betw. LL/LH & earth	250 V
Max. capacitance of wire ECG/lamp	120 pF


1) At 230 V<sub>AC</sub>

2) Minimum

3)  $t_{width} = 250 \mu s$  (measured at 50 %  $I_{peak}$ )

4) Type B

Dimensions & weight



Length	172.0 mm
Width	83.0 mm

## Product datasheet

Height	33.0 mm
Mounting hole spacing, length	163.0 mm
Cable cross-section, input side	0.75...1.5 / 0.75...2.5 mm <sup>2</sup> <sup>1)</sup>
Cable cross-section, output side	0.75...1.5 / 0.75...2.5 mm <sup>2</sup> <sup>1)</sup>
Wire preparation length, input side	5.5...6.5 mm
Wire preparation length, output side	5.5...6.5 mm
Product weight	290.00 g

<sup>1)</sup> With ferrule / Without ferrule

### Colors & materials

Casing material	Plastic
-----------------	---------

### Temperatures

Ambient temperature range	-15...+45 °C
Maximum temperature at tc test point	75 °C

### Lifespan

ECG lifetime	30000 h <sup>1)</sup>
--------------	-----------------------

<sup>1)</sup> At maximum T<sub>c</sub> / 10 % failure rate

### Additional product data

Design / version	With cable clamp
------------------	------------------

### Capabilities

Max. cable length to lamp/LED module	1.5 m
Overheating protection	Power reduction and switch off at T > 75 °C at the tc point
ECG reset time	> 0.5 s
Cable/wire types, input side	NYM-J 3x1.5 / NYM-J 3x2.5 / H05VV-F 3x1.5 / NHXMH-J 3x1.5 mm <sup>2</sup>
Cable/wire types, output side	SIHF-J 3x1.5 / SIHF-J 3x2.5 / SIHSI 3x1.0 mm <sup>2</sup>
Dimmable	No
Restriction on ignition time	20 min
Suitable for fixtures with prot. class	I

### Certificates & standards


Approval marks – approval	VDE / VDE-EMC / EAC / C-Tick
Type of protection	IP20
EEL – Energy Label	A2

# Product datasheet

## Standards

Acc. to EN 61347-2-12/Acc. to EN 55015/Acc. to EN 61000-3-2/Acc. to EN 61547/Acc. to EN 62493

## Wiring Diagram



Wiring diagram




## Thermal characteristics

Ballast losses and lamp heat radiation can lead to heat accumulation in a completely closed case. Therefore it is necessary to ensure that the temperature at the measuring point  $t_c$  of the ECG does not exceed the maximum value.

## Attention!








For safety reasons disconnect the device before replacing the lamp!

## Download Data

File	
	Tender Documents Tender Document for POWERTRONIC EVG.eng
	Certificates EMC-Marks approval
	Certificates VDE-Marks approval

## Product datasheet

---

	Certificates EAC PT family
	Declarations of conformity Declaration of conformity
	Installation/Operation notice Technical guide - POWERTRONIC for HID-lamps (GB)
	On-Pack-Info EAC - PTI I PT-FIT I
	CAD data 3-dim CAD PTI-FIT 3570 I
	CAD data 3-dim CAD PTI-FIT 3570 I
	CAD data 3-dim CAD PTI-FIT 3570 I

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321377685	PT-FIT 70/220...240 I	Shipping carton box 20	437 mm x 100 mm x 406 mm	17.74 dm <sup>3</sup>	6130.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.