



HIRSCHMANN

A BELDEN BRAND

Product information E08-CC3A1A-DF0500C1-XA500-AB

Industrial Connecting Solutions:Archive - Industrial Connectors:M8 Circular connector E-Series (Archive):with screw locking:Cable socket with integrally molded lead:E08-CC3A1A-DF0500C1-XA500-AB

<http://e-catalog.hirschmann.com/link/57078-24228-62529-24229-24233-24234-40126/en/conf/uistate>

Name E08-CC3A1A-DF0500C1-XA500-AB



Angled cable socket, with integrally molded lead, selfsecuring lock nut, cable length 5 m

Delivery informations

Availability no longer available

Product description

Description Angled cable socket, with integrally molded lead, selfsecuring lock nut, cable length 5 m

Type E08-CC3A1A-DF0500C1-XA500-AB

Order No. 934 556-002

Other standard types
cable material PUR 025:
cable length 2 m,
order no. 934 556-001;
cable length 10 m,
order no. 934 556-003

Type of contact female

Number of contacts 3

Cable material PVC

Cable color black

Cable length 5 m

Conductor size 0.25 mm²

Cable specification flexible lead

Cable type LiFYY

Standard IEC 61076-2-101 (Ed. 1)

Housing Color black

Technical data

Wire stranding 32 x 0.1

Rated voltage AC/DC 60 V

Rated current 4 A, notice UL and derating

Material

Contact material Cu Sn

Contact surface material Au

Contact bearer material PA

Housing material PUR

Coupling nut material Zn Al/Ni

O-Ring Viton

Environmental conditions

Protection class (IEC 60529) IP 65, IP 67, IP 68, IP 69K

Pollution severity 3

Temperature range -25 °C to +90 °C, notice derating

Inflammability class

Housing HB

Cable UL FT1

Contact bearer V0

Approvals

UL UL


Industrial Connecting Solutions:Archive - Industrial Connectors:M8 Circular connector E-Series (Archive):with screw locking:Cable socket with integrally molded lead:E08-CC3A1A-DF0500C1-XA500-AB
<http://e-catalog.hirschmann.com/link/57078-24228-62529-24229-24233-24234-40126/en/conf/ui.state>

Packing unit

Packaging unit 10 pieces

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.