



Principal dimensions			Basic load ratings		Fatigue load limit	Speed ratings		Mass	Designation
			dynamic	static		Reference speed	Limiting speed		
d	D	B	C	C ₀	P _u				
mm			kN		kN	r/min		kg	-
50	90	20	26,5	9,15	0,48	16000	10000	0,53	1210 EKTN9



Tapered bore, taper
1: 12

Calculation factors

e	0,21
Y_1	3
Y_2	4,6
Y_0	3,2