

Customer Information Sheet

DRAWING No:- M30-110XX00

SHEET 2 OF 2



IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm




NOTES:

1. TO BE USED IN CONJUNCTION WITH M30-1000006 OR M30-1010006 CRIMP CONTACTS. THE SPECIFICATIONS BELOW ARE APPROPRIATE WHEN USED WITH THESE CONTACTS.
2. SPECIFICATIONS:
 RATED CURRENT = 1 AMP AC/DC
 RATED VOLTAGE = 150V AC/DC
 TEMPERATURE RANGE = -55°C TO +85°C
 DIELECTRIC WITHSTANDING VOLTAGE = 500V (AC)
 INSULATING RESISTANCE = 1000 MEGOHMS MIN
3. MATES WITH M30-600XX06 AND M30-610XX06 PIN HEADERS.
4. ALL TOLERANCES ± 0.30 UNLESS OTHERWISE STATED.

ORDER CODE:

M30-110XX00

No. OF WAYS
02 TO 15



4	22.09.97	4091
3	26.03.97	3828
2	13.11.96	3612
1	03.06.96	----
ISS.	DATE	/N
APPROVED:		
CHECKED:		
DRAWN:	D. BECK	
CUSTOMER REF.		
ASSEMBLY DRG:		

HARWIN

HARWIN INC
U.S.A.
TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
UK.
TEL: 01705 370451
FAX: 01705 324010

HARWIN PTE
SINGAPORE
TEL: 65 7794909
FAX: 65 7793868

HARWIN CONNECTORS
KOREA
TEL: 822 521 0747
FAX: 822 521 0749

TOLERANCES

X. = $\pm 1mm$
 X.X = $\pm 0.25mm$
 X.XX = $\pm 0.10mm$
 X.XXX = $\pm 0.01mm$
 ANGLES = $\pm 1^\circ$
 UNLESS STATED

MATERIAL:

66 NYLON (UL94V-0)

FINISH: CLEAN

S/AREA: mm²

TITLE:

1.25mm PITCH SIL
CRIMP MOULDING

DRAWING NUMBER:

M30-110XX00

SHT
2
OF
2