


Cam followers



| Dimensions | | | | Basic load ratings | | Fatigue load limit | Maximum radial loads | | Limiting speed | Mass | Designation |
|------------|----|-----|----|--------------------|-----------------------|--------------------|------------------------|------------------------|----------------|------|-------------|
| D | d | B | C | dynamic C | static C ₀ | P _u | dynamic F _r | static F _{0r} | r/min | kg | - |
| mm | | | | kN | | kN | kN | | | | |
| 80 | 30 | 100 | 35 | 36,9 | 72 | 9 | 106 | 150 | 1800 | 1,61 | KR 80 PPA |



Appertaining grease nipple(s)

NIP A3x9.5

Appertaining hexagonal nut

Size, mm

M 30x1.5

Rec. tightening torque, Nm

450

Internal hexagon in stud

Key width, mm

14