





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			R2	REVISED PER ECO-08-019092	05AUG08	HMR	JO



RECOMENDED PC BOARD HOLE PATTERN
PC BOARD THICKNESS 1.57[.062]



- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED $0.76\mu\text{m}$ [.000030] GOLD IN CONTACT
AREA, $3.81-7.62\mu\text{m}$ [.000150-.000300] BRIGHT TIN-LEAD ON LEADS
ALL OVER $1.27\mu\text{m}$ [.000050] MINIMUM NICKEL
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO
CONTACT LOCATIONS
- 4 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN.
- 5 TOLERANCE IS NON-CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE LOGO.
- 7 POINT-OF-MEASUREMENT DIMENSION FOR PLATING
THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT-OF-CONTACT DIMENSION.
- 9 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 10 TE LOGO AND CSA LOGO ARE MOLDED INTO HOUSING.
- 11 CONTACT: DUPLEX PLATED $0.76\mu\text{m}$ [.000030] MIN GOLD IN CONTACT
AREA, $3.81-7.62\mu\text{m}$ [.000150-.000300] MATTE TIN ON LEADS
ALL OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL
- 12 ROHS 2002 /95/EC COMPLIANT.




	$\triangle_2$	99.06[3.900]	101.60[4.000]	80		4-534206-0
	$\triangle_2$	96.52[3.800]	99.06[3.900]	78		3-534206-9
	$\triangle_2$	93.98[3.700]	96.52[3.800]	76		3-534206-8
	$\triangle_2$	91.44[3.600]	93.98[3.700]	74		3-534206-7
	$\triangle_2$	88.90[3.500]	91.44[3.600]	72		3-534206-6
	$\triangle_2$	86.36[3.400]	88.90[3.500]	70		3-534206-5
	$\triangle_2$	83.82[3.300]	86.36[3.400]	68		3-534206-4
	$\triangle_2$	81.28[3.200]	83.82[3.300]	66		3-534206-3
	$\triangle_2$	78.74[3.100]	81.28[3.200]	64		3-534206-2
	$\triangle_2$	76.20[3.000]	78.74[3.100]	62		3-534206-1
	$\triangle_2$	73.66[2.900]	76.20[3.000]	60		3-534206-0
	$\triangle_2$	71.12[2.800]	73.66[2.900]	58		2-534206-9
	$\triangle_2$	68.58[2.700]	71.12[2.800]	56		2-534206-8
	$\triangle_2$	66.04[2.600]	68.58[2.700]	54		2-534206-7
	$\triangle_2$	63.50[2.500]	66.04[2.600]	52		2-534206-6
	$\triangle_2$	60.96[2.400]	63.50[2.500]	50		2-534206-5
	$\triangle_2$	58.42[2.300]	60.96[2.400]	48		2-534206-4
	$\triangle_2$	55.88[2.200]	58.42[2.300]	46		2-534206-3
	$\triangle_2$	53.34[2.100]	55.88[2.200]	44		2-534206-2
	$\triangle_2$	50.80[2.000]	53.34[2.100]	42		2-534206-1
	$\triangle_2$	48.26[1.900]	50.80[2.000]	40		2-534206-0
	$\triangle_2$	45.72[1.800]	48.26[1.900]	38		1-534206-9
	$\triangle_2$	43.18[1.700]	45.72[1.800]	36		1-534206-8
	$\triangle_2$	40.64[1.600]	43.18[1.700]	34		1-534206-7
	$\triangle_2$	38.10[1.500]	40.64[1.600]	32		1-534206-6
	$\triangle_2$	35.56[1.400]	38.10[1.500]	30		1-534206-5
	$\triangle_2$	33.02[1.300]	35.56[1.400]	28		1-534206-4
	$\triangle_2$	30.48[1.200]	33.02[1.300]	26		1-534206-3
	$\triangle_2$	27.94[1.100]	30.48[1.200]	24		1-534206-2
	$\triangle_2$	25.40[1.000]	27.94[1.100]	22		1-534206-1
	$\triangle_2$	22.86[.900]	25.40[1.000]	20		1-534206-0
	$\triangle_2$	20.32[.800]	22.86[.900]	18		534206-9
	$\triangle_2$	17.78[.700]	20.32[.800]	16		534206-8
	$\triangle_2$	15.24[.600]	17.78[.700]	14		534206-7
	$\triangle_2$	12.70[.500]	15.24[.600]	12		534206-6
$\triangle_9$	$\triangle_2$	10.16[.400]	12.70[.500]	10		534206-5
$\triangle_9$	$\triangle_2$	7.62[.300]	10.16[.400]	8		534206-4
$\triangle_9$	$\triangle_2$	5.08[.200]	7.62[.300]	6		534206-3
$\triangle_9$	$\triangle_2$	2.54[.100]	5.08[.200]	4		534206-2
$\triangle_9$	$\triangle_2$	-	2.54[.100]	2	$\triangle_6$	534206-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002 CHK 06NOV02 J.OLSON APVD 06NOV02 J.OLSON PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018 WEIGHT —		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
MATERIAL 		FINISH  		SIZE A2	CAGE CODE 00779
		DRAWING NO C-534206		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
				REV R2	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

9	1.1	99.06[3.900]	101.60[4.000]	80	1.2	9-534206-0
	1.1	96.52[3.800]	99.06[3.900]	78	1.2	8-534206-9
	1.1	93.98[3.700]	96.52[3.800]	76	1.2	8-534206-8
	1.1	91.44[3.600]	93.98[3.700]	74	1.2	8-534206-7
	1.1	88.90[3.500]	91.44[3.600]	72	1.2	8-534206-6
	1.1	86.36[3.400]	88.90[3.500]	70	1.2	8-534206-5
	1.1	83.82[3.300]	86.36[3.400]	68	1.2	8-534206-4
	1.1	81.28[3.200]	83.82[3.300]	66	1.2	8-534206-3
	1.1	78.74[3.100]	81.28[3.200]	64	1.2	8-534206-2
	1.1	76.20[3.000]	78.74[3.100]	62	1.2	8-534206-1
	1.1	73.66[2.900]	76.20[3.000]	60	1.2	8-534206-0
	1.1	71.12[2.800]	73.66[2.900]	58	1.2	7-534206-9
	1.1	68.58[2.700]	71.12[2.800]	56	1.2	7-534206-8
	1.1	66.04[2.600]	68.58[2.700]	54	1.2	7-534206-7
	1.1	63.50[2.500]	66.04[2.600]	52	1.2	7-534206-6
	1.1	60.96[2.400]	63.50[2.500]	50	1.2	7-534206-5
	1.1	58.42[2.300]	60.96[2.400]	48	1.2	7-534206-4
	1.1	55.88[2.200]	58.42[2.300]	46	1.2	7-534206-3
	1.1	53.34[2.100]	55.88[2.200]	44	1.2	7-534206-2
	1.1	50.80[2.000]	53.34[2.100]	42	1.2	7-534206-1
	1.1	48.26[1.900]	50.80[2.000]	40	1.2	7-534206-0
	1.1	45.72[1.800]	48.26[1.900]	38	1.2	6-534206-9
	1.1	43.18[1.700]	45.72[1.800]	36	1.2	6-534206-8
	1.1	40.64[1.600]	43.18[1.700]	34	1.2	6-534206-7
	1.1	38.10[1.500]	40.64[1.600]	32	1.2	6-534206-6
	1.1	35.56[1.400]	38.10[1.500]	30	1.2	6-534206-5
	1.1	33.02[1.300]	35.56[1.400]	28	1.2	6-534206-4
	1.1	30.48[1.200]	33.02[1.300]	26	1.2	6-534206-3
	1.1	27.94[1.100]	30.48[1.200]	24	1.2	6-534206-2
	1.1	25.40[1.000]	27.94[1.100]	22	1.2	6-534206-1
	1.1	22.86[.900]	25.40[1.000]	20	1.2	6-534206-0
	1.1	20.32[.800]	22.86[.900]	18	1.2	5-534206-9
1.1	17.78[.700]	20.32[.800]	16	1.2	5-534206-8	
1.1	15.24[.600]	17.78[.700]	14	1.2	5-534206-7	
1.1	12.70[.500]	15.24[.600]	12	1.2	5-534206-6	
1.1	10.16[.400]	12.70[.500]	10	1.2	5-534206-5	
9	1.1	7.62[.300]	10.16[.400]	8	1.2	5-534206-4
9	1.1	5.08[.200]	7.62[.300]	6	1.2	5-534206-3
9	1.1	2.54[.100]	5.08[.200]	4	1.2	5-534206-2
9	1.1	-	2.54[.100]	2	6 1.2	5-534206-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002 CHK J.OLSON 06NOV02		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD J.OLSON 06NOV02 PRODUCT SPEC 108-25022			
		APPLICATION SPEC 114-25018			
		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=534206 —			
MATERIAL 		FINISH 		WEIGHT — CUSTOMER DRAWING	
				SCALE 1:1 SHEET 2 OF 2 REV R2	