

## General Information

<b>Extended Product Type:</b>	MU10/13.SF2
<b>Product ID:</b>	1SNA199014R1100
<b>EAN:</b>	3472591990140
<b>Catalog Description:</b>	MU10/13.SF2 Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - Black
<b>Long Description:</b>	MU10/13.SF2 Screw Clamp Terminal Blocks Fuse

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

## Ordering

<b>EAN:</b>	3472591990140
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85361050

## Dimensions

<b>Product Net Width:</b>	13 mm
<b>Product Net Height:</b>	78 mm
<b>Product Net Depth:</b>	76 mm
<b>Product Net Weight:</b>	46 g

## Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	172 mm
<b>Package Level 1 Height:</b>	71 mm
<b>Package Level 1 Length:</b>	155 mm
<b>Package Level 1 Gross Weight:</b>	0.92 kg
<b>Package Level 1 EAN:</b>	3472591990140
<b>Package Level 2 Units:</b>	200 piece
<b>Package Level 3 Units:</b>	4800 piece
<b>Product Packing Type:</b>	Box

## Environmental

<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-08-01
---------------------	--

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity-Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 22 ... 10 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
<b>Flammability According to UL94:</b>	V0

## Additional Information

<b>Color:</b>	Black
<b>Connecting Capacity-Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5 ... 16 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Function:</b>	Fuse
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Product Main Type:</b>	MU10/13.SF
<b>Product Name:</b>	Terminal Block
<b>Rated Cross-Section:</b>	10 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 10 A
<b>Rated Voltage (U<sub>r</sub>):</b>	750 V
<b>Recommended Screw Driver:</b>	5.5 mm
<b>Spacing:</b>	13 mm
<b>Sub-Function:</b>	For 6.3x25 and 6.3x32 Fuses
<b>Tightening Torque:</b>	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

Wire Stripping Length: 12.0 mm

---

### Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information: 1SNC160001C0207-CH-A screw clamp

Declaration of Conformity - CE: 1SND225007C1007

EAC Certificate: 1SND161009A1100

RoHS Information: 1SND230023F0201

---

### Classifications

---

ETIM 4.0: EC000899 - Fuse terminal block

ETIM 5.0: EC000899 - Fuse terminal block

Object Classification Code: X

---