

192.CPE HIGH-PERFORMANCE DIAGONAL CUTTERS | 192.14CPE




Norm :

NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500

Description

- Cutting edges designed to cleanly cut all types of wire: piano wire, soft wires and modern materials (200 kg/mm²).
- Minimum cutting force thanks to long lever arm and offset axis.
- High durability Chrome-Molybdenum-Vanadium steel, very hard cutting edges 61/63 HRC.
- Ergonomic grips resistant to chemical agents.
- Removable return spring.
- Finish: chromed.



Information

B [mm]	21,5
C [mm]	15,5
E [mm]	9,5
L [mm]	145
[g]	160