

## Cable marker label - WML 7,5 (25X13)A4 - 0830691

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker label, Sheet, white, unlabeled, can be labeled with: Office printing systems, Mounting type: Adhesive, Cable diameter: ≤7.5 mm, Lettering field: 25 x 13 mm




The figure shows a similar product

### Why buy this product

- The cable marker labels consist of a self-adhesive marking field and a transparent protective foil
- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- Resistant to solvents



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 718769
Weight per Piece (excluding packing)	15.28 g
Custom tariff number	39199000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	31.75 mm
Width (a)	25 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

#### General

Note	Print image may vary depending on laser printer
Color	white
Base element material	Vinyl film

# Cable marker label - WML 7,5 (25X13)A4 - 0830691

## Technical data

### General

Components	Free from halogen and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	49
Number of individual labels per row	7
Adhesive	Acrylic
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Marking mounting type	Adhesive

## Classifications

### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

## Cable marker label - WML 7,5 (25X13)A4 - 0830691

### Classifications

#### UNSPSC

UNSPSC 13.2	39121410
-------------	----------