

# CCT16650

IHP'clíc - intuitive switch - 1 channel - 7D 24 H -  
6 years memory



## Main

|                                |  |
|--------------------------------|--|
| Range of product               | DuoLine  |
| Modular device name            | IHP'clíc   |
| Modular device type            | Intuitive switch   |
| Number of channels             | 1  |
| Battery type                   | Lithium  |
| Modular device additional info | Absence for holidays function<br>Automatic time changeover<br>Mechanical compatibility with electrical distribution comb busbars<br>Override controls On/Off |

## Complementary

|                                |  |
|--------------------------------|--|
| Cycle duration                 | 7 days<br>24 hours   |
| Bulb type                      | 230 V AC halogen lamp 2300 W<br>230 V AC incandescent lamp 2300 W<br>Dual mounted fluorescent tube conventional 10 2 x 58 W<br>Dual mounted fluorescent tube conventional 5 2 x 100 W<br>Dual mounted fluorescent tube electronic 5 2 x 36 W<br>Dual mounted fluorescent tube electronic 3 2 x 58 W<br>Fluocompact lamp electronic 9 7 W<br>Fluocompact lamp electronic 7 11 W<br>Fluocompact lamp electronic 7 15 W<br>Fluocompact lamp electronic 7 20 W<br>Fluorescent tube electronic 9 36 W<br>Fluorescent tube electronic 6 58 W<br>Non-corrected fluorescent tube 20 58 W<br>Non-corrected fluorescent tube 10 100 W<br>Non-corrected fluorescent tube 26 36 W<br>Parallel-corrected fluorescent tube conventional 10 36 W<br>Parallel-corrected fluorescent tube conventional 6 58 W<br>Parallel-corrected fluorescent tube conventional 2 100 W<br>Parallel-corrected mercury and sodium vapour lamps 250 W<br>Serial-corrected fluorescent tube 26 36 W<br>Serial-corrected fluorescent tube 20 58 W<br>Serial-corrected fluorescent tube 10 100 W |
| Power consumption              | 8.5 VA   |
| Maximum switching current      | 10 A 250 V AC 0.6<br>16 A 250 V AC 1   |
| [Ue] rated operational voltage | 230 V AC   |
| Display type                   | LCD  |
| Battery life                   | 5 yr   |
| Maximum number of switchings   | 28   |
| Minimum interval duration      | 1 min  |
| Backup time                    | 6 years time and program saving  |
| Product mounting               | DIN rail   |
| 9 mm pitches                   | 5  |
| Connections - terminals        | Screw terminal $\leq 6 \text{ mm}^2$   |
| Product weight                 | 0.145 kg   |

## Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -10...50 °C |
| IP degree of protection               | IP20 B      |