

## Datasheet

### **RS Pro 605 series Crimp Receptacle, 2.8 x 0.5mm, 0.3mm<sup>2</sup> to 1.25mm<sup>2</sup>, 22AWG to 16AWG, Tin Plated**

RS Stock No: **488-1213**



## Product Details

RS Pro crimp receptacle has 2.8 x 0.5 mm tab size and 0.3 to 1.25 mm<sup>2</sup>, 22 AWG to 16 AWG wire size with tin plating. It has a range of push-on terminals (F-Style) available in cable. It has PCB mount versions, with a selection of insulating covers available separately. The receptacle is available in 3 widths to fit 0.5 or 0.8 mm blades.

## Features and Benefits

- Receptacles are available in 3 widths to fit 0.5 or 0.8 mm blades
- Push-on terminals (F-Style) available in cable
- PCB mount versions, with a selection of insulating covers available separately

**Specifications:**

Connector Type	Tab
Contact Material	Brass
Contact Plating	Tin
Gender	Female
Insulation	Uninsulated
Length	16 mm
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm <sup>2</sup> )	1.25 mm <sup>2</sup>
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm <sup>2</sup> )	0.3 mm <sup>2</sup>
Tab Size	2.8 x 0.5 mm
Wire Size	0.34 to 1.4 mm <sup>2</sup>
Width	3.2 mm