



- ① HOUSING FULLY LOADED WITH CONTACTS.
- ② NUMBER ON CONTACT INDICATES WIRE RANGE.
- ③ CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- ④ .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑤ .000001 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑥ .000020 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑦ .000050 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑧ SPECIAL DATE CODE IN THIS APPROXIMATE AREA. A; MM = MONTH; Y = LAST DIGIT OF YEAR.
- ⑨ .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 MATTE TIN IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑩ .000001 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 MATTE TIN IN AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑪ OBSOLETE

STANDARD	.125 .115	⑩	2	#22-26	2-745495-0
STANDARD	.125 .115	⑨	3	#20-22	1-745495-9
STANDARD	.125 .115	⑨	2	#22-26	1-745495-8
STANDARD	.125 .115	⑨	1	#26-30	1-745495-7
SMALL PACK	.125 .115	⑤	2	#22-26	1-745495-6
STANDARD	.125 .115	⑦	2	#22-26	1-745495-4
STANDARD	.125 .115	⑥	2	#22-26	1-745495-3
STANDARD	.156 .146	⑤	3	#20-22	1-745495-2
			2	#22-26	1-745495-1
			1	#26-30	1-745495-0
STANDARD	.156 .146	④	3	#20-22	745495-9
			2	#22-26	745495-8
			1	#26-30	745495-7
STANDARD	.125 .115	⑤	3	#20-22	745495-6
			2	#22-26	745495-5
			1	#26-30	745495-4
STANDARD	.125 .115	④	3	#20-22	745495-3
			2	#22-26	745495-2
			1	#26-30	745495-1
PACKAGING	H	CONTACT FINISH	②	AWG WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J GALLUCCI BG 3-19-90		Tyco Electronics Corporation	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
0 PLC	± .005	APVD		NAME	
1 PLC	± .005	APVD		PRODUCT SPEC	
2 PLC	± .005	APVD		APPLICATION SPEC	
3 PLC	± .005	APVD		SIZE	
4 PLC	± .005	APVD		CAGE CODE	
ANGLES	± .005	APVD		DRAWING NO	
MATERIAL SEE CALL OUT	FINISH	WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV S	