

Enclosure:

Material / of the housing		metal
Color / of the top part of housing		yellow

Actuator:

Design of the operating mechanism		EMERGENCY-STOP
Material / of the activation element		metal
Manner of function / of the activation element / arresting lock		Yes
Manner of function / of the activation element / tentative		No

General technical details:

Product designation		enclosure for control and signaling units with standard fittings
Design of the product / with coat of paint		Yes
Operating current		
<ul style="list-style-type: none"> • at AC-15 / at 230 V <ul style="list-style-type: none"> • at 50 Hz / rated value • at 60 Hz / rated value • at DC-13 / at 24 V / rated value 	A	6 4 3
Operating voltage		
<ul style="list-style-type: none"> • for DC / rated value / maximum • for DC / rated value / minimum • 1 / for DC / rated value • 1 / at 50 Hz / for AC / rated value • 1 / at 60 Hz / for AC / rated value • at 50 Hz / at AC / rated value / minimum • at 50 Hz / at AC / rated value / maximum • at 60 Hz / at AC / rated value / minimum • at 60 Hz / at AC / rated value / maximum 	V	230 5 230 400 300 5 400 5 300
Type of voltage		
<ul style="list-style-type: none"> • of the operating voltage 		AC/DC
Number of key-operated switches		0
Number of selection switches		0
Number of mushroom pushbuttons		1
Number of control points		1

Number of indicator lights		0
Number of pushbuttons		0
Product function / emergency-OFF function		Yes
Supply status / pre-wired on terminal strip		No
Supply status / as a kit		No
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Item designation / according to DIN EN 61346-2		S
Design of the electrical connection		spring-loaded terminals
Type of fixing/fixation / for switching elements, socket fixing and accessories		floor mounting
Product component		
<ul style="list-style-type: none"> • stand/pedestal 		No
<ul style="list-style-type: none"> • protective collar 		Yes
Color / of the button		red

Auxiliary Contacts:

Number of NC contacts / for auxiliary contact		2
Number of NO contacts / for auxiliary contact		0
Number of change-over switches / for auxiliary contact		0

Installation/mounting/dimensions:

Type of fixing/fixation		screw fixing
Shape / of the installation hole		round
Mounting diameter	mm	22
Width	mm	85
Height	mm	85
Depth	mm	65

Ambient conditions:

Protection class IP		IP67
Ambient temperature		
<ul style="list-style-type: none"> • during the operating phase 	°C	-25 ... 70
Climatic class / according to DIN 50017		KTW24

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Global Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3801-2DJ3/all>

last change:

Aug 16, 2010