


BXTU ML2 BD S 0-180 (920 249)



Figure without obligation



Basic circuit diagram BXTU ML2 BD S 0-180




Diagram of the voltage protection level BXTU

Type	BXTU ML2 BD S 0-180
Part No.	920 249
SPD class	TYPE 1 PI
SPD monitoring system	LifeCheck
Operating voltage (U_N)	0-180 V
Frequency of the operating voltage (f_{UN})	0-400 Hz
Max. continuous operating d.c. voltage (U_C)	180 V
Max. continuous operating a.c. voltage (U_C)	127 V
Permissible superimposed signal voltage (U_{signal})	$\leq \pm 5$ V
Cut-off frequency line-line (U_{signal} , balanced 100 ohms) (f_c)	50 MHz
Nominal current at 80 °C (equal to max. short-circuit current) (I_n)	100 mA
D1 Total lightning impulse current (10/350 μ s) (I_{imp})	9 kA
D1 Lightning impulse current (10/350 μ s) per line (I_{imp})	2.5 kA
C2 Total nominal discharge current (8/20 μ s) (I_n)	20 kA
C2 Nominal discharge current (8/20 μ s) per line (I_n)	10 kA
Voltage protection level line-line for I_n C2 (U_p)	see diagram, line C2
Voltage protection level line-line at 1 kV/ μ s C3 (U_p)	see diagram, line C3
Voltage protection level line-line for I_{imp} D1 (U_p)	$\leq U_N + 53$ V
Voltage protection level line-PG for C2/C3/D1	≤ 550 V
Series resistance per line	≤ 10 ohms; typically 7.5 ohms
Capacitance line-line (C)	≤ 80 pF
Capacitance line-PG (C)	≤ 25 pF
Operating temperature range (T_U)	-40 °C ... +80 °C
Degree of protection (plugged-in)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21, UL 497B
SIL classification	up to SIL3 ^{*)}
Approvals	CSA, UL, GOST
Weight	23 g
Customs tariff number	85363010
GTIN	4013364127845
PU	1 pc(s)

^{*)} For more detailed information, please visit www.dehn-international.com.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.