


# brass tailpiece adaptors

## 0123 tailpiece adaptor for rubber hose, male BSP taper



brass




| ØD | C    |            | ØD1  | F  | L    | L1   | T <sub>mini</sub> | kg    |
|----|------|------------|------|----|------|------|-------------------|-------|
| 4  | R1/8 | 0123 04 10 | 6    | 10 | 34   | 22,5 | 3,3               | 0,008 |
| 6  | R1/8 | 0123 06 10 | 8    | 10 | 34   | 22,5 | 5                 | 0,009 |
| 7  | R1/8 | 0123 07 10 | 9    | 10 | 34   | 22,5 | 5                 | 0,009 |
| 7  | R1/4 | 0123 07 13 | 9    | 14 | 38,5 | 22,5 | 6                 | 0,018 |
| 7  | R3/8 | 0123 07 17 | 9    | 17 | 39   | 22,5 | 6                 | 0,023 |
| 10 | R1/8 | 0123 10 10 | 12,2 | 13 | 34   | 22,5 | 5                 | 0,014 |
| 10 | R1/4 | 0123 10 13 | 12,2 | 14 | 38,5 | 22,5 | 7                 | 0,021 |
| 10 | R3/8 | 0123 10 17 | 12,2 | 17 | 39   | 22,5 | 9,5               | 0,023 |
| 12 | R3/8 | 0123 12 17 | 14   | 17 | 46   | 29,5 | 11                | 0,026 |
| 13 | R1/4 | 0123 13 13 | 15   | 17 | 45,5 | 29,5 | 7                 | 0,027 |
| 13 | R3/8 | 0123 13 17 | 15   | 17 | 46   | 29,5 | 11                | 0,027 |
| 13 | R1/2 | 0123 13 21 | 15   | 22 | 50,5 | 29,5 | 12                | 0,047 |
| 16 | R3/8 | 0123 16 17 | 18,5 | 19 | 54,5 | 38   | 11                | 0,040 |
| 16 | R1/2 | 0123 16 21 | 18,5 | 22 | 59   | 38   | 14                | 0,056 |
| 16 | R3/4 | 0123 16 27 | 18,5 | 27 | 62   | 38   | 15                | 0,082 |
| 19 | R3/8 | 0123 19 17 | 21,5 | 22 | 54,5 | 38   | 11                | 0,046 |
| 19 | R1/2 | 0123 19 21 | 21,5 | 22 | 59   | 38   | 14                | 0,058 |
| 19 | R3/4 | 0123 19 27 | 21,5 | 27 | 62   | 38   | 18                | 0,083 |
| 25 | R3/4 | 0123 25 27 | 26,7 | 27 | 62   | 38   | 18                | 0,083 |
| 25 | R1"  | 0123 25 34 | 27   | 36 | 65   | 38   | 24                | 0,124 |
| 32 | R1"  | 0123 32 34 | 34,5 | 36 | 70   | 43   | 24                | 0,144 |

## 0136 tailpiece adaptor for Legris nylon tube, male BSP taper



brass



| ØD | C    |            | ØD1  | F  | L    | L1 | T <sub>mini</sub> | kg    |
|----|------|------------|------|----|------|----|-------------------|-------|
| 4  | R1/8 | 0136 06 10 | 4,3  | 10 | 26,5 | 15 | 2                 | 0,007 |
| 4  | R1/4 | 0136 06 13 | 4,3  | 14 | 31   | 15 | 2                 | 0,015 |
| 4  | R3/8 | 0136 06 17 | 4,3  | 17 | 31,5 | 15 | 2                 | 0,020 |
| 6  | R1/8 | 0136 08 10 | 6,4  | 10 | 26,5 | 15 | 4                 | 0,007 |
| 6  | R1/4 | 0136 08 13 | 6,4  | 14 | 31   | 15 | 4                 | 0,015 |
| 6  | R3/8 | 0136 08 17 | 6,4  | 17 | 31,5 | 15 | 4                 | 0,020 |
| 8  | R1/4 | 0136 10 13 | 8,4  | 14 | 31   | 15 | 6                 | 0,016 |
| 8  | R3/8 | 0136 10 17 | 8,4  | 17 | 31,5 | 15 | 6                 | 0,020 |
| 8  | R1/2 | 0136 10 21 | 8,4  | 22 | 36   | 15 | 6                 | 0,039 |
| 10 | R1/4 | 0136 12 13 | 10,7 | 14 | 36   | 20 | 7                 | 0,019 |
| 10 | R3/8 | 0136 12 17 | 10,7 | 17 | 36,5 | 20 | 8                 | 0,023 |
| 10 | R1/2 | 0136 12 21 | 10,7 | 22 | 41   | 20 | 8                 | 0,040 |
| 12 | R1/4 | 0136 14 13 | 12,7 | 14 | 36   | 20 | 7                 | 0,019 |
| 12 | R3/8 | 0136 14 17 | 12,7 | 17 | 36,5 | 20 | 10                | 0,023 |
| 12 | R1/2 | 0136 14 21 | 12,7 | 22 | 41   | 20 | 10                | 0,042 |
| 12 | R3/4 | 0136 14 27 | 12,7 | 27 | 44   | 20 | 10                | 0,072 |
| 13 | R3/8 | 0136 16 17 | 13,7 | 17 | 36,5 | 20 | 11                | 0,023 |
| 13 | R1/2 | 0136 16 21 | 13,7 | 22 | 41   | 20 | 11                | 0,041 |
| 13 | R3/4 | 0136 16 27 | 13,7 | 27 | 44   | 20 | 11                | 0,071 |

The 2 central digits in the product code part number represent the tube outside ØD. Ex: 0136 16 27.  
This range of adaptors is limited to the maximum size (16 x 13) of Legris nylon tube.

### Technical specification of brass accessories :

- **Working pressure :** 250 bar maximum  
The maximum pressure and temperature varies according to the nature of the fluid, and the diameter and type of tube used.
- **Working temperature :** with captive seal: -20° to +80°C  
without captive seal: -40° to +150 °C