

Differential Preamplifier

ADA400A Data Sheet



ADA400A

Features & Benefits

- Active Differential Preamplifier
- 10 $\mu\text{V}/\text{div}$ Sensitivity
- Typically 100 dB CMRR DC to 10 kHz
- Integral Probe Power with TEKPROBE™ BNC

Applications

- Mechanical Analysis
- Audio Design
- Biomedical Research (Not Certified For Patient Connection)
- Medical Equipment (Not Certified For Patient Connection)

ADA400A

The ADA400A Differential Preamplifier allows direct oscilloscope measurements of very low amplitude voltages and signals which are not ground referenced. The high impedance of both inputs eliminates the need to add additional ground points in the DUT, thereby avoiding circulating currents which disturb the measurement or the circuit.

The high gain and extremely high common mode rejection provide usable measurements of voltages as low as 5 μV , even in high-noise environments. Selectable bandwidth limiting reduces normal mode noise from digital logic, switch mode power supplies, and line frequency sources. Adjustable differential offset allows the user to null out transducer bridge bias and galvanic potential from the test setup. An "infinite impedance" mode can be selected in the two highest gain ranges allowing accurate measurements of signals with high source impedance.

The ADA400A is powered directly from TDS400, TDS500, TDS600, TDS700, TDS5000, TDS7000 (TEKPROBE), TDS7000 (TekConnect) w/ TCA-1MEG Series oscilloscopes. It may also be powered by a 1103 Probe Power Supply.

ASEAN / Australasia (65) 6356 3900

Austria +41 52 675 3777

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777

Belgium 07 81 60166

Brazil +55 (11) 40669400

Canada 1 (800) 661-5625

Central East Europe, Ukraine, and the Baltics +41 52 675 3777

Central Europe & Greece +41 52 675 3777

Denmark +45 80 88 1401

Finland +41 52 675 3777

France +33 (0) 1 69 86 81 81

Germany +49 (221) 94 77 400

Hong Kong (852) 2585-6688

India (91) 80-42922600

Italy +39 (02) 25086 1

Japan 81 (3) 6714-3010

Luxembourg +44 (0) 1344 392400

Mexico, Central/South America & Caribbean 52 (55) 54247900

Middle East, Asia, and North Africa +41 52 675 3777

The Netherlands 090 02 021797

Norway 800 16098

People's Republic of China 86 (10) 6235 1230

Poland +41 52 675 3777

Portugal 80 08 12370

Republic of Korea 82 (2) 6917-5000

Russia & CIS +7 (495) 7484900

South Africa +27 11 206 8360

Spain (+34) 901 988 054

Sweden 020 08 80371

Switzerland +41 52 675 3777

Taiwan 886 (2) 2722-9622

United Kingdom & Ireland +44 (0) 1344 392400

USA 1 (800) 426-2200

For other areas contact Tektronix, Inc at: 1 (503) 627-7111

Updated 30 October 2008

Characteristics

Gain – 100x, 10x, 1x, .01x.

CMRR – ≥100,000: 1 DC - 10 kHz.

Gain	CM Range	Differential Range*1	Max Offset
100	±10 V	0.1 V	±1.0 V
10	±10 V	1 V	±1.0 V
1	±40 V	10 V	±40 V
0.1	±40 V	80 V	±40 V

*1 For higher voltages, attenuating probes may be used, but CMRR performance will be degraded.

Bandwidth Limits – 100 Hz, 3 kHz, 100 kHz, full (≥1 MHz).

Input Impedance – 1 MΩ || ~ 55 pF (infinity Ω selectable in 100x and 10x gains).

Noise – Typically ≤30 μV_{RMS} at 100x gain (referred to input).

Ordering Information

ADA400A

Differential Preamplifier.

Includes: Instruction manual (Order 070-9164-01), 2 spare input fuses (Order 159-0024-xx).

Service

Opt. C3 – Calibration Service 3 Years.

Opt. C5 – Calibration Service 5 Years.

Opt. D1 – Calibration Data Report.

Opt. D3 – Calibration Data Report 3 Years (with Opt. C3).

Opt. D5 – Calibration Data Report 5 Years (with Opt. C5).

Opt. R5 – Repair Service 5 Years.

Recommended Accessories

P6101B 1x passive probe (2 recommended).

CE Marking Not Applicable.



Product(s) are manufactured in ISO registered facilities.

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com



Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.