

battery type: Lithium - Manganese-Dioxide
battery size: IEC: 6AM6; ANSI: 1604LC; LA522; 9V-Block
chemical system: Li-MnO₂

Conditions

nominal voltage: 9 V
open circuit voltage: 9.3...10.2 V new battery
 9.3...10.2 V after 1 year storage at 20°C

capacity
rated: 1100 mAh all measurements at 23°C ambient
 discharge at 1mA load; 24h/d
 End Voltage (EV): 5.4V

minimum: 950 mAh discharge at 10mA load; 24h/d
 End Voltage (EV): 5.4V

900 mAh discharge at 50mA load; 24h/d
 End Voltage (EV): 5.4V

typical service output (new batteries)

≥ 65 h load resistor: 600Ω; EV: 5.4V
 discharge 24h/d

≥ 30 h load resistor: 270Ω; EV: 5.4V
 discharge 1h/d

≥ 70 h load resistor: 620Ω; EV: 5.4V
 discharge 2h/d

max. continuous
discharge current: 600 mA

max. peak
discharge current: 1000 mA

internal resistance: ≤ 2 Ω at 1kHz, sine wave measurement
 (new battery) according to IEC 896-2

shelf life: 10 years under proper storage conditions

leakage resistance

over discharge: no leakage 180ohms continuous discharge for 48h; ta: 20°C; RH: 60±15%
high temperature: no leakage store 20days at ta: 60°C; RH:90±5%

ambient temperature
range: - 40...60 °C

recommended storage
conditions: -20....30 °C ambient temperature
 45...75 % rel. humidity





mechanical specifications

cell dimensions

length L1: 26.5 -1 mm
 length L2: 17.5 -2 mm
 length L3: 12.7 ± 0.25 mm
 height h1: 48.5 -2 mm
 weight: 33 ± 3 g

carton box

dimensions (L x W x H): 82 x 27 x 51 mm
 weight (incl. batteries): 185 ± 5 g



ANSMANN Specifications for model:

data sheet no. / part no.

supplier no.

author / date

Ansmann Lithium Industrial Battery
9V - E-Block 5pcs box

1505-0002

703331

TG / 02.03.2015