

Thursday, 22 November 2012



www.sks-kontakt.de

News contact sitemap Login

main menu

- home
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
  - ▶ 0,64 mm system
  - ▶ 2 mm system
  - ▶ 4 mm system
  - ▶ 4 mm sliding sleeve system
  - ▶ 4 mm safety system
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ clamp-type test probes ▶ clamp-type test probe ▶ KLEPS 2600

KLEPS 2600

datasheet for KLEPS 2600  
article number: 972306100



View Full-Size Image

search online catalogue



Search

Search

Messetermine

SPS/IPC/DRIVES  
27. 11. 2012 - 29. 11. 2012

Newsletter Anmeldung

Test & Measurement  
 First Name Name  
 E-mail  
 Subscribe

QR-Code



product description:	order number: 972 306-100
<b>description:</b>	Safety clamp-type test probe with rotating grip jaws and flexible shaft. Wires and pins with up to a maximum diameter of 4mm can be clamped thanks to the special form of the grip jaws. 4mm diameter brass socket connection.
<b>typ:</b>	KLEPS 2600 schwarz/black
<b>system:</b>	4mm safety system
<b>order number:</b>	972 306-100
<b>clamping range:</b>	4 mm
<b>clamping typ:</b>	rotating grip jaws
<b>color</b>	
<b>other color versions:</b>	
technical data	
<b>measurement category acc. to IEC 61010:</b>	CAT III
<b>norm</b>	IEC 61010
<b>type of termination:</b>	4 mm socket (unsprung)
<b>rated voltage:</b>	AC/DC 1000 V
<b>rated current:</b>	4 A
<b>Please consider derating curve!</b>	
<b>contact resistance:</b>	10 mOhm
material	
<b>contact material:</b>	grip jaws: spring steel socket: brass
<b>contact surface material:</b>	grip jaws: tin
<b>housing material:</b>	PBT
environmental conditions:	
<b>temperature range:</b>	-25 °C to +80 °C
<b>inflammable class:</b>	
<b>housing (basic material):</b>	UL 94 HB
drawing	

© 2012 www.sks-kontakt.de

Joomla! is Free Software released under the GNU General Public License.