

**Ordering number** C11607\_ANNA-50-3-M

Family	Anna-50-3	FWHM	20 degrees
Type	Lens array	Efficiency	90 %
LED	NF2x757A	cd/lm	4.080
Color	Clear	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

**NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.**



**PRODUCT DATASHEET**  
**Anna-50-3 series**  
last update 16/4/2012



**GENERAL INFORMATION**

- Product series especially designed & optimized for NF2x757A series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

[http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94\\_Yellow%20Card.pdf](http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf)

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>



Material: PMMA

- Versions:  
 Anna-3-S  
 Anna-3-M  
 Anna-3-W  
 Anna-4-S  
 Anna-4-M  
 Anna-4-W  
 Anna-5-S  
 Anna-5-M  
 Anna-5-W  
 Anna-6-S  
 Anna-6-M  
 Anna-6-W  
 Anna-7-S  
 Anna-7-M  
 Anna-7-W

Number of cones varies;  
 3, 4, 5, 6 and 7 pcs  
 on bottom side depending  
 the version.

This drawing is our property.  
 It can't be reproduced  
 or communicated without  
 our written agreement.



DRAWING TITLE

DRAWN BY p		DATE 05.10.2010		Datasheet Anna50-series Lens			
CHECKED BY t k		DATE 03.08.2010		SIZE A4	DRAWING NUMBER -		REV 1
DESIGNED BY hh		DATE 30.07.2010		SCALE 1:1	WEIGHT (g)	SHEET 1/1	

4

3

2

1

4

3


2

1

D

A

Luminaire: Ledil Oy C11607\_ANNA-50-3-M-757 (Nichia 757 97lm @ 100mA) LOR=90%  
Lamps: 1 x Nichia 757 97lm @ 100mA



cd/klm

— C0 - C180

— C90 - C270