

Label - EML (100X73)R YE - 0817138

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Label, Roll, yellow, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 100 x 73 mm

Why buy this product

- A wide range of marker sizes and colors are available for custom designs
- Precise printing quality and good adhesive properties
- If high-quality ink ribbons are used, the labeling is resistant to solvents and suitable for use even under harsh industrial conditions
- The EML ... materials are UL-listed
- The special packaging protects rolls that have already been started from the dirt found in industrial environments
- The EML ... self-adhesive device markers have been specifically developed for marking various types of operating equipment in control, system, and control cabinet engineering

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 107761 |
| Weight per Piece (excluding packing) | 555.5 g |
| Custom tariff number | 39199000 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|--------|
| Length (b) | 100 mm |
| Width (a) | 73 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Ambient temperature (assembly) | > 5 °C |
| Recommended storage conditions | 21 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing. |

General

| | |
|------------|--------------------------------|
| Color | yellow |
| Components | free from silicone and halogen |
| Material | Polyester |

Label - EML (100X73)R YE - 0817138

Technical data

General

| | |
|---|-------------------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 300 |
| Number of individual labels per row | 1 |
| RoHS compliant | Yes |
| Adhesive | Acrylic |
| Printability | Thermal transfer |
| Device | 5146477 THERMOMARK ROLL |
| | 5146723 THERMOMARK ROLL X1 |
| | 5146231 THERMOMARK X1.2 |
| | 5146257 THERMOMARK S1.1 |
| Ink ribbon | 5145384 THERMOMARK-RIBBON 110 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | Following DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result | Test passed |
| Foil strength | 55 µm |
| Adhesive strength | 20 µm |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
|----------|----------|

Label - EML (100X73)R YE - 0817138

Classifications

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Approvals

Approvals


Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details

| |
|---|
| UL Recognized  |
|---|

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

