






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		J1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



1. WIRE RANGE 0.13–0.35 mm² (26–22 AWG).
 2. INSULATION RANGE: 0.89–1.65 [.035–.065] DIA LARGER SIZES OF 0.68–1.91 [.066–.075] DIA INSULATION REQUIRE WIRE AND CRIMP EVALUATION FROM AMP INCORPORATED.
 3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. 0.00076 [.000030] MIN THK GOLD STRIPES IN LOCALIZED PLATE AREA ON BEAM AND DIMPLE OVER 0.00127 [.000050] MIN THK NICKEL OVER ENTIRE CONTACT
- OR—
- OR GOLD FLASH OVER PALLADIUM–NICKEL STRIPES, .00076 [.000030] MIN THK TOTAL IN LOCALIZED PLATE AREA ON BEAM AND DIMPLE OVER .00127 [.000050] MIN NICKEL OVER ENTIRE CONTACT.
5. AFTER PACKAGING AND SHIPMENT, A LANCE HEIGHT 0.46–0.71 [.018–.030] IS PERMISSABLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG T. BECK		01MAR91	 PRE-TIN		770666-2	
		CHK R. SWING		01MAR91			770666-1	
					FINISH		PART NO.	
					 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		RECEPTACLE, CST-100, LOOSE PIECE —		
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13 [.005] 4 PLC ± — ANGLES ± —		DWG D. CLARK APVD PRODUCT SPEC APPLICATION SPEC —		SIZE A1		
MATERIAL 0.198 [.0078] PH BRZ		FINISH SEE TABLE		WEIGHT —		CAGE CODE 007796		DRAWING NO C-770666
				CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1
						REV		J