

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1998

© COPYRIGHT 1998

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC
JDIST
J

REVISIONS

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	O	RELEASED	FJD0-0414-04	11NOV 2004	T.S	D.M
	O1	ADDITION PART NO	ECR-07-007149	28MAR 2007	M.M	D.M



D

D



シリーズマーク
SERIES MARK

AMP マーク
AMP MARK



推奨基板取付け寸法 (公差: ±0.05)

PC 基板厚: 1.6±0.3


(コネクタ搭載面)

RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)

PC BOARD THICKNESS:1.6±0.3
(CONNECTOR MOUNT SIDE)

C

C

1747994-2
(KEYING Y)

NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK

TAB CONTACT: COPPER ALLOY

RETENTION LEG: BRASS

△ FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING△ FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

注記

1. 材料: ハウジング: ガラス入り熱可塑性
ポリエステル樹脂 (94V-0), 色: 黒

タブ コンタクト: 銅合金

リテンション レグ: 黄銅


△ めっき: コンタクト: 全面Ni下地
接触部: 0.38μm MIN金めっき△ めっき: リテンションレグとコンタクト半田付部
: ニッケル下地の上にスズめっき

B

B

A

A

1747994-1
(KEYING X)

SCALE:2-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T.Sakamoto 11/NOV/04		Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: mm		CHK D.Mitsugi 11/NOV/04		NAME 2列 ヘッダーアセンブリー 16P	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD D.Mitsugi 11/NOV/04		<垂直タイプ> DOUBLE ROW HEADER ASS'Y 16P ("V"TYPE) <DYNAMIC D-2100D>	
一般公差 102 : ±0.3 302 : ±0.35 1002 : ±0.4 ANGLE : ±3°		PRODUCT SPEC 108-5619		SIZE A3	
MATERIAL 材料 注記参照 SEE NOTES		APPLICATION SPEC 114-5258		CAGE CODE 00779	
FINISH 仕上 注記参照 SEE NOTES		WEIGHT		DRAWING NO C-1747994	
CUSTOMER DRAWING		SCALE 4-1		SHEET 1 OF 2	
				REV 01	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1998

© COPYRIGHT 1998

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

変更

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
		SEE SHEET 1 OF 2				


D

D



シリーズマーク
SERIES MARK

AMP マーク
AMP MARK



		回路番号							
		1	2	3	4	5	6	7	8
列番号	B	① Ground	② Signal	② Signal	① Ground	② Signal	② Signal	② Signal	② Signal
	A	② Signal	② Signal	② Signal	② Signal	② Signal	② Ground	② Signal	① Ground

POINT OF SEQUENTIAL
1-1747994-1

NOTES

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK

TAB CONTACT: COPPER ALLOY

RETENTION LEG: BRASS

△2 FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING

△3 FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

1. 材料: ハウジング: ガラス入り熱可塑性

ポリエステル樹脂 (94V-0), 色: 黒

タブ コンタクト: 銅合金

リテンション レグ: 黄銅

△2 めっき: コンタクト: 全面Ni下地

接触部: 0.38μm MIN金めっき

△3 めっき: リテンションレグとコンタクト半田付部

: ニッケル下地の上にスズめっき

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. Sakamoto 11/NOV/'04		Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位 長 mm		CHK D. Mitsugi 11/NOV/'04		NAME 2列 ヘッダーアセンブリー 16P	
TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10 ±0.3 30 ±0.35 100 ±0.4 ANGLE ±3°		APVD D. Mitsugi 11/NOV/'04		製品規格 108-5619	
MATERIAL 材料 注記参照 SEE NOTES		FINISH 仕上 注記参照 SEE NOTES		APPLICATION SPEC 取付適用規格 114-5258	
WEIGHT		SIZE A3		CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO C-1747994		RESTRICTED TO —	
SCALE 尺 4-1		SHEET 2 OF 2		REV 01	