


## DG PCB NPE (952 650)

- Integration of DEHNguard protection modules in the PCBs of electronic/electrical devices
- Easy and flexible use for all circuit configurations
- Coded base part and protection module ensure against installing an incorrect module



Figure without obligation



Dimension drawing DG PCB NPE

Einpoliger Sockel zur Montage auf Geräteleiterplatten für DEHNguard Module

Type	DG PCB NPE
Part No.	952 650
Associated protection module	DG MOD NPE (Part No. 952 050)
Max. continuous a.c. voltage (module)	255 V
Operating temperature range (T <sub>U</sub> )	-40°C...+80°C
For mounting on	directly soldered into PCB
Enclosure material	thermoplastic, red, UL 94 V-2
Weight	18 g
Customs tariff number	85366930
GTIN	4013364149823
PU	72 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.