

## Housing - HC-D 15-SMLD-52/O2PG16 - 1672686

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Box mounting base, with single locking latch, height 52 mm, without screw connection, 2x Pg16, with protective covers

The illustration shows version, HC-D 15-SML-52/M 1 PG 16 without protective cover



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 145224
Weight per Piece (excluding packing)	283.6 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	52 mm
Width	50 mm
Length	93 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65 (When plugged in)
	IP54 (mit geschlossenem Schutzdeckel)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-D15, A10
Type	D15
Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable outlets	2

# Housing - HC-D 15-SMLD-52/O2PG16 - 1672686

## Technical data

### General

Cable exit	Lateral
Screw connection	none
Type of the screw connection	2x Pg16
Protective cover	Yes
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Material lock	Steel, galvanized

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC / GL

---

Ex Approvals

# Housing - HC-D 15-SMLD-52/O2PG16 - 1672686

## Approvals

Approvals submitted

Approval details

EAC

GL

## Drawings

Dimensional drawing

