

DULUX D 18 W/830

OSRAM DULUX D | CFLni, 2 tubes, with 2-pin base for CCG operation



Areas of application

- Offices, public buildings
- Shops
- Supermarkets and department stores
- Hotels, restaurants
- Industry

Product benefits

- Extremely economical
- Good quality of light
- Excellent luminous flux
- Long service life
- Improved maintenance

Product features

- Average life: 10,000 h
- Color rendering index R_a : 80...89
- Short and compact pin-base lamp with double-turn tubes
- Single-ended two-pin plug-in G24d base



Product datasheet

Technical data


Electrical data

Nominal wattage	18.0 W
-----------------	--------

Photometrical data

Light color	830
Light color as per EN 12464-1	LUMILUX Warm White
Luminous flux at 25 °C	1200 lm
Luminance	4.5 cd/cm ²
Color rendering group	1B

Dimensions & weight



Tube diameter	12 mm
Length	153.0 mm
Length acc. to IEC standard	140 mm

Lifespan


Lifespan	10000 h ¹⁾
----------	-----------------------

¹⁾ With CCG/LLCG

Additional product data

Base (standard designation)	G24d-2
Appropriate disposal acc. to WEEE	Yes

Light Distribution




Spectral power distribution

Equipment / Accessories

- Suitable for operation on conventional control gear

Safety advice

In case of lamp breakage: www.osram.com/brokenlamp



Circuit diagram

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300025704	DULUX D 18 W/830	Shipping carton box 10	153 mm x 174 mm x 119 mm	3.17 dm ³	645.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.