


GO THROUGH SCREWDRIVER - PHILLIPS

PART NO.	SLOTTED	L MM	A MM	B MM			G.W. (kg)
61703	#2x100mm	221	35.5	6.0	12	180	5.8
61705	#2x150mm	271	35.5	6.0	12	180	5.8
61706	#3x150mm	272	39.0	8.0	6	72	4.9
61707	#3x200mm	322	39.0	8.0	6	72	6.7
61708	#3x250mm	372	39.0	8.0	6	72	11.9


ANSI B107.15
DIN 5264



T-SERIES POZI

PART NO.	SIZE	L MM	A MM	B MM			G.W. (kg)
61901	PZ0x75mm	159	26.0	3.0	12	144	4.8
61902	PZ1x100mm	200	28.0	5.0	12	144	8.8
61903	PZ1x150mm	250	28.0	5.0	12	144	10.1
61904	PZ2x100mm	214	34.6	6.0	12	144	14.2
61905	PZ2x150mm	264	34.6	6.0	12	144	16.1
61906	PZ3x150mm	264	34.6	6.0	12	96	13.6


ANSI B107.15
DIN 5264



T-SERIES SLOTTED

PART NO.	SLOTTED	L MM	A MM	B MM			G.W. (kg)
63402	3.0x75mm	159	26.0	3.0	12	144	4.8
63403	3.0x100mm	184	26.0	3.0	12	144	5.2
63404	3.0x150mm	233	23.5	3.0	12	144	5.8
63405	3.0x200mm	283	23.5	3.0	12	144	6.2
63407	5.0x75mm	175	28.0	5.0	12	144	8.3
63408	5.0x100mm	200	28.0	5.0	12	144	8.8
63409	5.0x150mm	250	26.0	5.0	12	144	10.1
63410	5.0x200mm	300	26.0	5.0	12	144	11.4
63411	6.0x38mm	98	35.5	6.0	12	144	8.3
63412	6.0x100mm	214	34.6	6.0	12	144	14.2
63413	6.0x150mm	264	34.6	6.0	12	144	16.1
63414	6.0x200mm	315	34.0	6.0	12	96	12.2
63415	6.0x250mm	365	34.0	6.0	12	96	13.3
63416	8.0x150mm	265	35.5	8.0	12	96	13.6
63417	8.0x200mm	314	34.6	8.0	12	96	15.8


ANSI B107.15
DIN 5265



T-SERIES PHILLIPS

PART NO.	SLOTTED	L MM	A MM	B MM			G.W. (kg)
63502	#0x75mm	159	26.0	3.0	12	144	4.8
63503	#0x100mm	183	23.5	3.0	12	144	5.2
63504	#0x150mm	233	23.5	3.0	12	144	5.8
63505	#0x200mm	283	23.5	3.0	12	144	6.2
63507	#1x75mm	175	28.0	5.0	12	144	8.3
63508	#1x100mm	200	28.0	5.0	12	144	8.8
63509	#1x150mm	250	26.0	5.0	12	144	10.1
63510	#1x200mm	300	28.0	5.0	12	144	11.1
63511	#2x38mm	99	36.0	6.0	12	144	8.3
63512	#2x100mm	214	34.6	6.0	12	144	14.2
63513	#2x150mm	264	34.6	6.0	12	144	16.1
63514	#2x200mm	315	34.0	6.0	12	96	12.2
63515	#2x250mm	364	34.6	6.0	12	96	13.3
63516	#3x150mm	264	34.6	8.0	12	96	13.6
63517	#3x200mm	314	34.6	8.0	12	96	15.8

ANSI B107.15
DIN 5262



T-SERIES DUAL HEAD

PART NO.	DUAL HEAD	L MM	A MM	B MM			G.W. (kg)
66202	#2&6mmx38mm	99	36.0	6.4	12	72	5.1
66203	#1&5mmx100mm	214	34.6	6.4	12	72	8.0
66204	#2&6mmx100mm	214	34.6	6.4	12	72	8.0
66205	#1&5mmx150mm	264	34.6	6.4	12	72	9.0
66206	#2&6mmx150mm	264	34.6	6.4	12	72	9.0

ANSI B107.15
DIN 5264


⚠ Nature of this product is subject to wear and tear upon usage.
Not covered under Lifetime Warranty.



INSULATED PHILLIPS

PART NO.	PHILLIPS	L MM	A MM	B MM	C MM			G.W. (kg)
61211	#0x60mm	148	26.0	4.8	3.0	10	500	18.9
61212	#1x80mm	188	32.4	6.2	4.5	10	280	20.7
61213	#2x100mm	210	32.4	7.8	6.0	10	280	20.5
61214	#3x150mm	266	36.0	9.7	8.0	10	200	20.1

- ROD is made of chrome-vanadium-molybdenum
- Soft-grip handle is made of TPR and PP material
- Soft-grip handle comes in dual colour
- Meets DIN standards, VDE and GS certification
- Up to 1000V
- Made in Germany



INSULATED SLOTTED

PART NO.	SLOTTED	L MM	A MM	B MM	C MM			G.W. (kg)
61311	2.5x75mm	162	26.0	4.5	2.5	10	500	20.7
61312	3x100mm	188	25.9	4.9	3.0	10	500	20.7
61313	4x100mm	208	32.3	6.2	4.0	10	280	20.5
61314	5.5x125mm	232	32.3	6.9	5.0	10	200	17.8
61315	6.5x150mm	258	32.4	7.5	5.5	10	200	20.1

- ROD is made of chrome-vanadium-molybdenum
- Soft-grip handle is made of TPR and PP material
- Soft-grip handle comes in dual colour
- Meets DIN standards, VDE and GS certification
- Up to 1000V
- Made in Germany

