

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

A1

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

B3

REVISED PER ECO-11-005027

06APR11

RK

HMR

CROSS REFERENCE LIST / UEBERSETZUNGSLISTE

TE CONNECTIVITY PART NO.	OLD PART NUMBER	SEE SHEET		TE CONNECTIVITY PART NO.	OLD PART NUMBER	SEE SHEET
1 393 546 - 1	C42315-A1347-A101	2		2 1-1 393 546 - 1	C42315-A1347-A112	2
1 393 546 - 2	C42315-A1347-A102	2		2 1-1 393 546 - 2	C42315-A1347-A116	2
1 393 546 - 3	C42315-A1347-A103	2		1 - 1 393 546 - 3	C42315-A1347-A124	2
1 393 546 - 4	C42315-A1347-A104	2		1 - 1 393 546 - 4	C42315-A1347-A201	3
1 393 546 - 5	C42315-A1347-A105	2		1 - 1 393 546 - 5	C42315-A1347-A202	3
2 1-393 546 - 6	C42315-A1347-A106	2		1 - 1 393 546 - 6	C42315-A1347-A203	3
1 393 546 - 7	C42315-A1347-A107	2		1 - 1 393 546 - 7	C42315-A1347-A204	3
1 393 546 - 8	C42315-A1347-A108	2		2 1-1 393 546 - 8	C42315-A1347-A205	3
1 393 546 - 9	C42315-A1347-A109	2		1 - 1 393 546 - 9	C42315-A1347-A208	3
1 - 1 393 546 - 0	C42315-A1347-A110	2		2 - 1 393 546 - 0	C42315-A1347-A212	3


ERSETZT EC-ZEICHNUNG C42315-A1347-A1***-27 BL. 1 UND 2
UND
C42315-A1347-A2***-27 BL. 1

2

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±

±

±

±

±°

-

MATERIAL

-

DWN

24 JAN 2001

G.ACKERMANN

CHK

M.SCHLEIHAUF

APVD

G.FELDMEIER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

1

OF

3

REV

B3

TE Connectivity

NAME

DIPFIX - SCHALTER
DIPFIX - SWITCH

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1393546-1

RESTRICTED TO

-

Pro/ENGINEER DRAWING

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

-

-


SEE SHEET 1

-

-



-

View A




1) Beim Kleinmaß 5,08 müssen die
Schalter spiegelbildlich montiert werden
In the case of dim. 5,08 the switches
have to be mounted rear side to rear side

Sollbruchstellen, einzelne
Verbindungen abtrennbar
Predetermined breaking point,
single connection units could be broken off



Rasterlochung
u. Packungsdichte

Mounting holes and
possible package density



Schaltschema

(Beispiel: 8 Verbindungsmöglichkeiten)



Circuit schematic
(example: 8 connections)



2

2

2

TE CONNECTIVITY
PART NO.

OLD PART NUMBER

DIMENSION
a

POSITION NUMBER
POLZAHL

1 393 546 - 1	C42315-A1347-A101	2.54	1
1 393 546 - 2	C42315-A1347-A102	5.08	2
1 393 546 - 3	C42315-A1347-A103	7.62	3
1 393 546 - 4	C42315-A1347-A104	10.16	4
1 393 546 - 5	C42315-A1347-A105	12.7	5
1 393 546 - 6	C42315-A1347-A106	15.24	6
1 393 546 - 7	C42315-A1347-A107	17.78	7
1 393 546 - 8	C42315-A1347-A108	20.32	8
1 393 546 - 9	C42315-A1347-A109	22.86	9
1 - 1 393 546 - 0	C42315-A1347-A110	25.4	10
1 - 1 393 546 - 1	C42315-A1347-A112	30.48	12
1 - 1 393 546 - 2	C42315-A1347-A116	40.64	16
1 - 1 393 546 - 3	C42315-A1347-A124	60.96	24

MATERIAL: PBTP-GF30; COLOUR: NATURE

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	PL ±
	1 P/C ±
	2 P/C ±0.15
	3 P/C ±
	PL ±
	ANGLES ±1°
MATERIAL	FINISH
-	-

DWN 24 JAN 2001 G. ACKERMANN			
CHK - M. SCHLEIHAUF			
APVD - G. FELDMEIER		NAME	
PRODUCT SPEC		DIPFIX - SCHALTER DIPFIX - SWITCH	
APPLICATION SPEC		-	
WEIGHT		SIZE	RESTRICTED TO
-		A3	-
CUSTOMER DRAWING		CAGE CODE	REV
-		00779	B3
SCALE 5:1, 2:1		DRAWING NO	SHEET
-		C=1393546-1	2 OF 3

ERSETZT EC-ZEICHNUNG C42315-A1347-A1**-*-27 BL. 1 UND 2



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

-

-


SEE SHEET 1

-

-

-


View A



1) Beim Kleinmaß 5,08 müssen die
Schalter spiegelbildlich montiert werden
In the case of dim. 5,08 the switches
have to be mounted rear side to rear side


2) ausgeliefert in ausgehaktem Zustand
delivered in unlocked condition

Sollbruchstellen, einzelne
Schalter abtrennbar
Predetermined breaking point,
single switches could be broken off



Rasterlochung und
Packungsdichte

Mounting holes and
possible package density



Schaltschema
(Beispiel: 4 Umschalter)



Circuit schematic
(example: 4 changeover switches)



2

TE CONNECTIVITY PART NO.	OLD PART NUMBER	DIMENSION a	POSITION NUMBER POLZAHL
1 - 1 393 546 - 4	C42315-A1347-A201	5.08	1
1 - 1 393 546 - 5	C42315-A1347-A202	10.16	2
1 - 1 393 546 - 6	C42315-A1347-A203	15.24	3
1 - 1 393 546 - 7	C42315-A1347-A204	20.32	4
1 - 1 393 546 - 8	C42315-A1347-A205	25.4	5
1 - 1 393 546 - 9	C42315-A1347-A208	40.64	8
2 - 1 393 546 - 0	C42315-A1347-A212	60.96	12

ERSETZT EC-ZEICHNUNG C42315-A1347-A2***-27 BL.1

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±°
MATERIAL	FINISH
-	-

DWN	24 JAN 2001
CHK	G. ACKERMANN
APVD	M. SCHLEIHAUF
PRODUCT SPEC	G. FELDMEIER
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	

TE

TE Connectivity

NAME	DIPFIX - SCHALTER DIPFIX - SWITCH
SIZE	A3
CAGE CODE	00779
DRAWING NO	C=1393546-1
RESTRICTED TO	-
SCALE	5:1, 2:1
SHEET	3
OF	3
REV	B3