


7764



Description:

The disposable heel grounder is ideal for outfitting visitors in ESD controlled areas. An aluminum strip clips onto the shoe to make contact with the wearer. The conductive non-woven nylon strip is held to the heel of the shoe by pressure sensitive adhesive.

Electrical Performance:


1. The tab to cup resistance: $1 \times 10^4 - 1 \times 10^5$ ohms
2. Decay time: < 0.01 second (FTMS 101C, M4046C)

Item #	Description	Length	Pkg.
24165	Foot Ground, Heel, Disposable	12"	100
24167	Foot Ground, Boot, Disposable	20"	100

Refer to Tech Brief PS-2035 for a comparison of all Plastic Systems foot grounders

To Attach:

1. Strip release paper off pressure sensitive adhesive
2. Fold and clip aluminum strip to top of shoe or boot (between shoe and sock)
3. Pull strap snugly down and under heel
4. Step firmly onto pressure-sensitive adhesive and tear off excess material
serration
5. Check for proper ground connection with Item 41200 Combination Wrist Strap/Footwear Tester
6. One heel grounder should be used on each foot.



Foot Ground, Heel, Disposable



PLASTIC SYSTEMS
 261 CEDAR HILL STREET
 MARLBORO, MA 01752 USA
 TEL. (508)486-7390 FAX (508) 480-0267

DRAWING NUMBER

24165

DATE

8-22-94