

ZXMN3B14F


30V N-CANNEL ENHANCEMENT MODE MOSFET 2.5V GATE DRIVE

SUMMARY

$V_{(BR)DSS}=30V$; $R_{DS(on)}=0.08\Omega$; $I_D=3.5A$

DESCRIPTION

This new generation of Trench MOSFETs from Zetex utilizes a unique structure that combines the benefits of low on-resistance with fast switching speed. This makes them ideal for high efficiency, low voltage, power management applications.




PACKAGE

FEATURES

- Low on-resistance
- Fast switching speed
- Low threshold
- Low gate drive
- SOT23 package

APPLICATIONS


- DC-DC converters
- Power management functions
- Disconnect switches
- Motor control



ORDERING INFORMATION

DEVICE	REEL SIZE	TAPE WIDTH	QUANTITY PER REEL
ZXMN3B14FTA	7"	8mm	3,000 units
ZXMN3B14FTC	13"	8mm	10,000 units

PINOUT



DEVICE MARKING

- 3B4

ZXMN3B14F

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DSS}	30	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current @ $V_{GS} = 4.5V$; $T_A = 25^\circ C$ ^(b) @ $V_{GS} = 4.5V$; $T_A = 70^\circ C$ ^(b) @ $V_{GS} = 4.5V$; $T_A = 25^\circ C$ ^(a)	I_D	3.5 2.9 2.9	A A A
Pulsed Drain Current ^(c)	I_{DM}	16	A
Continuous Source Current (Body Diode) ^(b)	I_S	2.4	A
Pulsed Source Current (Body Diode) ^(c)	I_{SM}	16	A
Power Dissipation at $T_A = 25^\circ C$ ^(a)	P_D	1	W
Linear Derating Factor		8	mW/ $^\circ C$
Power Dissipation at $T_A = 25^\circ C$ ^(b)	P_D	1.5	W
Linear Derating Factor		12	mW/ $^\circ C$
Operating and Storage Temperature Range	T_j, T_{stg}	-55 to +150	$^\circ C$

THERMAL RESISTANCE

PARAMETER	SYMBOL	VALUE	UNIT
Junction to Ambient ^(a)	$R_{\theta JA}$	125	$^\circ C/W$
Junction to Ambient ^(b)	$R_{\theta JA}$	83	$^\circ C/W$

NOTES


(a) For a device surface mounted on 25mm x 25mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.

(b) For a device surface mounted on FR4 PCB measured at $t \leq 5$ sec.

(c) Repetitive rating - 25mm x 25mm FR4 PCB, $D=0.02$, pulse width 300 μs - pulse width limited by maximum junction temperature.

ZXMN3B14F

TYPICAL CHARACTERISTICS



ZXMN3B14F

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)


PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS
STATIC						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	30			V	I _D = 250μA, V _{GS} =0V
Zero Gate Voltage Drain Current	I _{DSS}			1	μA	V _{DS} = 30V, V _{GS} =0V
Gate-Body Leakage	I _{GSS}			100	nA	V _{GS} =± 12V, V _{DS} =0V
Gate-Source Threshold Voltage	V _{GS(th)}	0.7			V	I _D = 250μA, V _{DS} =V _{GS}
Static Drain-Source On-State Resistance ⁽¹⁾	R _{DS(on)}			0.080	Ω	V _{GS} = 4.5V, I _D = 3.1A
				0.140	Ω	V _{GS} = 2.5V, I _D = 2.2A
Forward Transconductance ^{(1) (3)}	g _{fs}		8.5		S	V _{DS} = 15V, I _D = 3.1A
DYNAMIC ⁽³⁾						
Input Capacitance	C _{iss}		568		pF	V _{DS} = 15V, V _{GS} =0V f=1MHz
Output Capacitance	C _{oss}		101		pF	
Reverse Transfer Capacitance	C _{rss}		66		pF	
SWITCHING ^{(2) (3)}						
Turn-On-Delay Time	t _{d(on)}		3.6		ns	V _{DD} = 15V, V _{GS} = 4.5V I _D = 1A R _G ≅ 6.0Ω
Rise Time	t _r		4.9		ns	
Turn-Off Delay Time	t _{d(off)}		17.3		ns	
Fall Time	t _f		9.8		ns	
Total Gate Charge	Q _g		6.7		nC	V _{DS} = 15V, V _{GS} = 4.5V I _D = 3.1A
Gate-Source Charge	Q _{gs}		1.4		nC	
Gate Drain Charge	Q _{gd}		1.8		nC	
SOURCE-DRAIN DIODE						
Diode Forward Voltage ⁽¹⁾	V _{SD}		0.82	0.95	V	T _j =25°C, I _S = 3.1A, V _{GS} =0V
Reverse Recovery Time ⁽³⁾	t _{rr}		10.8		ns	T _j =25°C, I _F = 1.6A,
Reverse Recovery Charge ⁽³⁾	Q _{rr}		4.54		nC	di/dt=100A/μs

NOTES

- (1) Measured under pulsed conditions. Pulse width $\leq 300\mu\text{s}$; duty cycle $\leq 2\%$.
(2) Switching characteristics are independent of operating junction temperature.
(3) For design aid only, not subject to production testing.


ZXMN3B14F

N-CHANNEL TYPICAL CHARACTERISTICS




ZXMN3B14F

N-CHANNEL TYPICAL CHARACTERISTICS




ZXMN3B14F

PACKAGE OUTLINE



PAD LAYOUT



Controlling dimensions are in millimetres. Approximate conversions are given in inches

PACKAGE DIMENSIONS

DIM	MILLIMETRES		INCHES		DIM	MILLIMETRES		INCHES	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
A	2.67	3.05	0.105	0.120	H	0.33	0.51	0.013	0.020
B	1.20	1.40	0.047	0.055	K	0.01	0.10	0.0004	0.004
C	—	1.10	—	0.043	L	2.10	2.50	0.083	0.0985
D	0.37	0.53	0.015	0.021	M	0.45	0.64	0.018	0.025
F	0.085	0.15	0.0034	0.0059	N	0.95 NOM		0.0375 NOM	
G	1.90 NOM		0.075 NOM		Θ	10° TYP		10° TYP	

© Zetex Semiconductors plc 2005

Europe	Americas	Asia Pacific	Corporate Headquarters
Zetex GmbH Streitfeldstraße 19 D-81673 München Germany Telefon: (49) 89 45 49 49 0 Fax: (49) 89 45 49 49 49 europa.sales@zetex.com	Zetex Inc 700 Veterans Memorial Hwy Hauppauge, NY 11788 USA Telephone: (1) 631 360 2222 Fax: (1) 631 360 8222 usa.sales@zetex.com	Zetex (Asia) Ltd 3701-04 Metroplaza Tower 1 Hing Fong Road, Kwai Fong Hong Kong Telephone: (852) 26100 611 Fax: (852) 24250 494 asia.sales@zetex.com	Zetex Semiconductors plc Zetex Technology Park Chadderton, Oldham, OL9 9LL United Kingdom Telephone (44) 161 622 4444 Fax: (44) 161 622 4446 hq@zetex.com

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

For the latest product information, log on to www.zetex.com

ISSUE 2 - JANUARY 2006