

SPECIFICATION SHEET



Talento 994



Antenna DCF 77

Talento 900 series

PRODUCT/ORDER CODE

Talento 991 single channel	1 x 16 amperes
Talento 992 two channel	2 x 16 amperes
Talento 993 three channel	3 x 16 amperes
Talento 994 four channel	4 x 16 amperes

General information

These products are suitable for din-rail mounting.

There are two optional accessories:

- wall-mounting kit
- panel mounting kit

Features common to all products are:

- Annual, weekly and daily programming and control
- Central European Time synchronisation via separate antenna
- 400 programme spaces
- Built-in lithium cell giving 6 year reserve.
- Integrated infra-red interface (see Talento *taxi* information)
- Automatic summer / winter changeover.
- Impulse & cycle output facility programmable in one second increments

Technical specification:

Dimensions	45 x 108 x 60 (6-modules)
Panel cut-out (panel kit required)	46 x 111mm
Weight	600g
AC switching capacity:	
- resistive load	16A 250v AC
- inductive load $\cos \phi$ 0.6	2.5A 250v AC
- incandescent lamp load	1000W
Contact type	1,2,3 or 4 volt-free changeover
Minimum switching time	1 second
Programmable	Every minute
Ambient temperature	-25°C to +55°C
Accuracy	typically + / - 2.5 seconds/day @ 20°C
Manual override	Advance on / off or Fix on / Fix off (advance on / off is self-resetting)

