



6 & 8 VERSIONS

8 VERSION SHOWN



DIM.	TYPE	POS. 4	POS. 6		POS. 8
		4 CKTS.	4 CKTS.	6 CKTS.	8 CKTS.
A		(11.18) / .440	(13.21) / .520	(13.21) / .520	(15.24) / .600
C		(7.62) / .300	(10.16) / .400	(10.16) / .400	(11.43) / .450
B		(3.81) / .150	(3.81) / .150	(6.35) / .250	(8.89) / .350


NOTES :

1- MATERIAL:

-HOUSING: LCP GLASS FILLED UL 94V-0,
COLOUR BLACK.

2- SEE OTHER NOTES SHEET 1

OPTIONAL KEYING



(0.10) / .004 Y

ADDED DIM TABLE	DESCRIPTION	REV
EC NO: E2008-0176	2007/10/05	
DRWN:DBYRNES	2007/10/05	
CHKD:	2007/10/05	
APPR:EOMAHONY	2007/10/05	

QUALITY SYMBOLS
▽=0
▽=0



GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .006
2 PLACES	± 0.15	± .010
1 PLACE	± 0.25	± ---
ANGULAR ± ---°		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS


DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM/IN	4:1	METRIC	
DRAWN BY	DATE	TITLE	
DBYRNES	2006/08/02	R/A LOW PROFILE PC JACK 4,6,8 CKTS SIZE SMT VERSION	
CHECKED BY	DATE		
EOMAHONY	2006/08/12		
APPROVED BY	DATE		
EOMAHONY	2006/08/12		
MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
	SD-95501-001	2 OF 5	

SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
A3	

4 VERSION ONLY



TYPE DIM.	POS. 4	POS. 6		POS. 8
	4 CKTS.	4 CKTS.	6 CKTS.	8 CKTS.
Y $\pm 0.05 / \pm .002$	(7.62) / .300	(10.16) / .400	(10.16) / .400	(11.43) / .450
X $\pm 0.05 / \pm .002$	(3.81) / .150	(3.81) / .150	(6.35) / .250	(8.89) / .350



NOTE:
FOR CONVECTION SOLDERING: DIA 3.25 $\pm$ 0.05 / .128 $\pm$.002
FOR WAVE SOLDERING: DIA 3.20 $\pm$ 0.10 / .126 $\pm$.004

MODIFIED TABLE EC NO: E2008-0176 DRWN: DBYRNES CHKD: APPR: EOMAHONY		DESCRIPTION	REV	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				▽=0 ▽=0										
					mm	INCH	DRAWN BY	DATE	TITLE R/A LOW PROFILE JACK PC JACK 4,6,8 CKT SIZE SMT AND STANDARD VERSION					
					4 PLACES	± ---	± ---	DBYRNES						
			3 PLACES	± ---	± .006	CHECKED BY	DATE	MOLEX MOLEX INCORPORATED						
			2 PLACES	± 0.15	± .010	EOMAHONY	2006/08/12							
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE	DOCUMENT NO. SD-95501-001						
			ANGULAR ± ---°			EOMAHONY	2006/08/12							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		SHEET NO.		3 OF 5				
						SEE CHART SHEETS 4,5&6								
						SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

SPECIAL PACKAGING TUBE,SEE PACKAGING SPEC PK95001 SHEET 3

PART NO FOR JACK ASSEMBLY
THROUGH HOLE VERSION

PART NO FOR JACK ASSEMBLY
SMT VERSION

HOUSING SIZE	LOADED CONTACTS	PLATING	LOP GLASS FILED 94V0,COLOR BLACK.							
			NO KEY	TOOLED	KEY	TOOLED		TOOLED		TOOLED
			NOT RIBBED		NOT RIBBED					
4	4	2	95501-2401	X						
6	4	2	95501-2601	X						
6	6	2	95501-2611	X						
8	8	2	95501-2821	X						

PLATING	LOP GLASS FILLED 94V0 COLOUR BLACK								
	NO KEY	TOOLED	KEY	TOOLED	NO KEY	TOOLED	KEY	TOOLED	
	NOT RIBBED		NOT RIBBED		NOT RIBBED		NOT RIBBED		
2	95501-6449	X							
2	95501-6649	X							
2	95501-6669	X							
2	95501-6889	X	95501-6890	X					

REMOVED GREY OPTIONS EC NO: E2007-0513 2007/01/08 DRWN:DBYRNES CHKD: 2007/01/08 APPR:EOMAHONY 2007/01/09	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		▽=0 ▽C=0		mm	INCH	DRAWN BY	DATE	TITLE LOW PROFILE R/A JACK STANDARD AND SMT VERSION TUBE PACKAGING			
			4 PLACES	± ---	± ---	DBYRNES	2006/08/02				
			3 PLACES	± ---	± ---	CHECKED BY	DATE				
			2 PLACES	± ---	± ---	EOMAHONY	2006/08/12				
			1 PLACE	± ---	± ---	APPROVED BY	DATE				
		ANGULAR ± ---°		EOMAHONY	2006/08/12	molex MOLEX INCORPORATED					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.			DOCUMENT NO.			SHEET NO.			
		SEE CHART			SD-95501-001			5 OF 5			
B	REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					