



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® HC Modular 250 Crimp terminal	09 11 001 3021	09 11 001 3121		

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm																
		Male contacts (M)	Female contacts (F)																		
Crimp contacts* Silver plated	35	09 11 000 6127	09 11 000 6227																		
	50	09 11 000 6128	09 11 000 6228																		
	70	09 11 000 6129	09 11 000 6229																		
PE crimp contacts	35	09 11 000 6104	09 11 000 6204																		
<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Tool identification</th> <th>Stripping length</th> <th>Ø</th> </tr> </thead> <tbody> <tr> <td>35 mm²</td> <td>12</td> <td>22 mm</td> <td>8,45 mm</td> </tr> <tr> <td>50 mm²</td> <td>14</td> <td>22 mm</td> <td>10,25 mm</td> </tr> <tr> <td>70 mm²</td> <td>16</td> <td>22 mm</td> <td>11,75 mm</td> </tr> </tbody> </table> <p>* for stranded wire acc. to IEC 60 228 class 5</p>						Wire gauge	Tool identification	Stripping length	Ø	35 mm ²	12	22 mm	8,45 mm	50 mm ²	14	22 mm	10,25 mm	70 mm ²	16	22 mm	11,75 mm
Wire gauge	Tool identification	Stripping length	Ø																		
35 mm ²	12	22 mm	8,45 mm																		
50 mm ²	14	22 mm	10,25 mm																		
70 mm ²	16	22 mm	11,75 mm																		

Tools	09 99 000 0332	09 99 000 0332	
-------	----------------	----------------	--

* Crimp zone acc. to DIN EN 46 235