

## Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 16 A, Rated voltage (III/2): 320 V, Number of positions: 5, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Mounting: Soldering, COMBICON connectors may only be activated under no load conditions. If for operating reasons small loads must be switched, experimental values are available upon request.




The figure shows a 10-position version of the product

### Why buy this product

- Double steel spring as extra safety against contact corrosion
- Inverted 16 A (HC) headers with socket contact for shock-proof applications or PCB/PCB connections
- Vibration-resistant connection by means of threaded flange (-GF)



### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 50 pc   |
| Minimum order quantity               | 50 pc   |
| GTIN                                 | <br>4 017918 878580 |
| Weight per Piece (excluding packing) | 4.52 g  |
| Custom tariff number                 | 85366990  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|             |          |
|-------------|----------|
| Length      | 19 mm    |
| Pitch       | 5.08 mm  |
| Dimension a | 20.32 mm |

#### General

|                             |                  |
|-----------------------------|------------------|
| Range of articles           | IC 2,5 HC/...-GF |
| Insulating material group   | I                |
| Rated surge voltage (III/3) | 4 kV             |
| Rated surge voltage (III/2) | 4 kV             |
| Rated surge voltage (II/2)  | 4 kV             |

## Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

### Technical data

#### General

|   |        |
|---|--------|
| Rated voltage (III/3)                   | 320 V  |
| Rated voltage (III/2)                   | 320 V  |
| Rated voltage (II/2)                    | 630 V  |
| Connection in acc. with standard        | EN-VDE |
| Nominal current I <sub>N</sub>          | 16 A   |
| Maximum load current                    | 16 A   |
| Insulating material                     | PA     |
| Inflammability class according to UL 94 | V0     |
| Color                                   | green  |
| Number of positions                     | 5      |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

---

#### Approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCEB Scheme / CCA / EAC / cULus Recognized

---

# Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

## Approvals

Ex Approvals

Approvals submitted

### Approval details

|                    |       |       |
|--------------------|-------|-------|
| UL Recognized      |       |       |
|                    | B     | D     |
| Nominal current IN | 16 A  | 10 A  |
| Nominal voltage UN | 250 V | 300 V |

|   |       |
|---|-------|
| VDE Gutachten mit Fertigungsüberwachung |       |
| Nominal current IN                      | 16 A  |
| Nominal voltage UN                      | 250 V |

|                    |       |       |
|--------------------|-------|-------|
| cUL Recognized     |       |       |
|                    | B     | D     |
| Nominal current IN | 16 A  | 10 A  |
| Nominal voltage UN | 250 V | 300 V |


|                    |       |
|--------------------|-------|
| IECEE CB Scheme    |       |
| Nominal current IN | 16 A  |
| Nominal voltage UN | 250 V |

|                    |       |
|--------------------|-------|
| CCA                |       |
| Nominal current IN | 16 A  |
| Nominal voltage UN | 250 V |

|     |  |
|-----|--|
| EAC |  |
|-----|--|

## Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

### Approvals

cULus Recognized 

### Accessories

Accessories

Coding element

Coding profile - CP-MSTB - 1734634



Coding profile, is inserted into the slot on the plug or inverted header, red insulating material

### Insulating sleeve

Insulating sleeve - MPS-IH WH - 0201663



Insulating sleeve, Color: white

Insulating sleeve - MPS-IH RD - 0201676



Insulating sleeve, Color: red

Insulating sleeve - MPS-IH BU - 0201689



Insulating sleeve, Color: blue

## Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

### Accessories

Insulating sleeve - MPS-IH YE - 0201692



Insulating sleeve, Color: yellow

---

Insulating sleeve - MPS-IH GN - 0201702



Insulating sleeve, Color: green

---

Insulating sleeve - MPS-IH BK - 0201731



Insulating sleeve, Color: black

---

Test plug terminal block

Reducing plug - RPS - 0201647



Reducing plug, Color: gray

---

Test plugs - MPS-MT - 0201744



Test plugs, Color: silver

---

Additional products

## Base strip - IC 2,5 HC/ 5-GF-5,08 - 1943454

### Accessories


Printed-circuit board connector - FKIC 2,5 HC/ 5-STF-5,08 - 1942730



Plug component, Nominal current: 16 A, Rated voltage (III/2): 320 V, Number of positions: 5, Pitch: 5.08 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin, COMBICON connectors may only be activated under no load conditions. If for operating reasons small loads must be switched, experimental values are available upon request.

### Drawings

Drilling diagram



Dimensioned drawing

