


	TECHNICAL DATA SHEET		code	MRG1791
			version	2
			date	2006-10-29
	Coax RG179 PE PVC		page	1/2

APPLICATION

Coaxial communication cable based on MIL-C-17.

CONSTRUCTION



1	Inner conductor	Silver plated, copper clad steel
2	Dielectric	Solid PE
3	Braid	Tinned copper
4	Sheath	PVC according the European Standard HD 624.

REQUIREMENTS AND TEST METHODS

Test methods in accordance with European standard EN 50289.

Mechanical characteristics

1. Inner conductor.	7 x 0.1 mm
Diameter:	0.3 mm ± 0.02 mm
2. Dielectric:	
Diameter:	1.6 mm ± 0.15 mm
3. Outer conductor:	
Diameter screen:	2.0 mm ± 0.15 mm
Coverage braid:	85 % ± 4 %
4. Sheath:	
Diameter:	2.8 mm ± 0.1 mm
5. Cable:	
Storage/operating temperature:	-25°C to +70°C
Minimum installation temperature:	-5 °C

	TECHNICAL DATA SHEET		code	MRG1791
			version	2
			date	2006-10-29
	Coax RG179 PE PVC		page	2/2

Electrical characteristics

Mean characteristic impedance:	$75 \pm 3 \Omega$
Regularity of impedance:	$> 40 \text{ dB}$
DC resistance inner conductor:	$\leq 802 \text{ Ohm/km}$
Capacitance:	$67 \text{ pF/m} \pm 3 \text{ pF/m}$
Nominal velocity of propagation:	66%
Voltage Rating	
DC:	2.0 kVdc
RMS	1.0 kVrms

Nominal Attenuation:

10 MHz:	15 dB/100m
100 MHz:	27 dB/100m
1000 MHz:	85 dB/100m

REVISIONS

#	Description	Date	Initials



Belden declares this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.