



mecalectro

Electromagnet for retaining or handling parts – 5.84.01



Diameter: 75 mm

Holding force when power on: 200 daN

Power Consumption: 14.5 W

Total mass: 1200 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 12 to 220Vcc

Duty Cycle: Permanent (100%)

Standard: NF C 79300

Examples of applications: Maintaining parts, blocking parts, positioning, gripping.