

3M™ Static Control Anti-Fatigue Mat 9900 Series

Static Control Anti-Fatigue Mats enable workers to stand comfortably for long periods while minimizing the fatigue associated with standing work. Manufactured from durable rubber, Anti-Fatigue Mats consist of a matrix of hollow cylinders that function like a spring when compressed. These mats provide a durable cushion that is designed to offer secure, stable footing and an energizing responsiveness.


Their structure provides a stable surface supported by rubber cells that soften in response to surface activity. These cells provide some of the most effective cushioning solutions because the Static Control Anti-Fatigue Mats get softer as compressed, not harder like products made of foam.



At Rest



Under impact



Rebound

Part Number	Description	3M ID Number
9900	3 ft. x 5 ft. (0.9 m x 1.5 m) Static Control Anti-Fatigue Mat	98-0798-5635-1
9900	2 ft. x 3 ft. Static Control Anti-Fatigue Mat	98-0798-5748-2
9910	3 ft. x custom length Static Control Anti-Fatigue Runner	98-0798-5636-9
9920	22 in. Octagonal Shape Static Control Anti-Fatigue Mat	98-0798-5674-0

One 3M™ Ground Cord 3040, 15 ft. (4.6 m) is included with each mat.

Property	Typical Value
Size	Standard: 3 ft. x 5 ft. (0.9 m x 1.5 m) , 2 ft. x 3 ft. (0.6 m x 0.9 m) and Octagonal 22 in. (55.9 cm) diameter Runners: 3 ft. width x custom length
Thickness	0.600 inches (1.52 cm) with beveled edge
Durometer	46 Shore A
Composition	SBR Rubber Polymers
Cleaning	Sweep, vacuum or damp mop
Color	Black
Edges	Solid molded rubber
Resistance:	
Surface to Ground Snap (RTG)	<1 x 10 ⁵ Ω
Surface to Ground (RTT)	<2 x 10 ⁵ Ω
Warranty	3 years limited warranty

**Tested per ESD STMS7.1*

Mats are easy to install and can be used at assembly and manufacturing workstations, warehouse and shipping areas, medical laboratories and in field service.



3M™ Static Control Anti-Fatigue Mat 9900 Series

3M is a trademark of 3M Company. All other trademarks are owned by their respective companies.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for three years from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1565-2 JHA