

MR16 HOME CLFT 12V 35W 30° GU5.3 SV

0022555

Range features



PRODUCT OVERVIEW

Ordering number	0022555
Light colour	829 Warm white
Technology	Halogen
Energy class	B
Average life (Rated) (h)	3000
Lamp finish	Aluminium
Lamp shape	Reflector
Dimmable	Yes
Cap/Base	GU5.3
Type	MR16
EAN code	5410288225555
CRI (Ra)	100
Beam angle(°)	30
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	500
Watt (Nominal) (W)	35
Equivalent watt (W)	No
Voltage (V)	12

MR16 HOME CLFT 12V 35W 30° GU5.3 SV

0022555

DATA TABLE

General data

Technology	Halogen
Ordering number	0022555
Energy class	B
Energy saving lamp	No
Average life (Rated) (h)	3000
Average life (Nominal) (h)	3000
Lamp shape	Reflector
Lamp finish	Aluminium
Dimmable	Yes
Cap/Base	GU5.3
Type	MR16
EAN code	5410288225555
Product name	MR16 HOME CLFT 12V 35W 30° GU5.3 SV
Lamp mercury content (mg)	0
Starting time (max) (s)	0
Warm-up time to 60% of full light (max) (s)	Instant Full Light
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-3
IEC Reference 3	IEC 60630
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 12000
Special purpose lamp	No
Transformer required	Yes

Optical data

Light colour	829 Warm w hite
CRI (Ra)	100
Suitable for accent lighting	Yes
Beam angle(°)	30
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	500
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	500
Peak intensity (cd)	1500

MR16 HOME CLFT 12V 35W 30° GU5.3 SV**0022555**

Electrical data

Watt (Rated) (W)	35
Equivalent watt (W)	No
Watt (Nominal) (W)	35
Voltage (V)	12
Lamp power factor	1

Physical data

Lamp Length (mm) - C/L	45
Max. Lamp Diameter (mm) - D	50
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No