

Machined contacts #16

Part numbers						Wire size		Max. wire Ø	Max. insul. Ø	Wire strip length
Standard contacts		Longer contacts		Shorter contacts		AWG	mm ²			
Male	Female	Male	Female	Male	Female					
RM20M12K	RC20M12K	RM20M12GE1K	RC20M12GE1K	RM20M12GE3K	RC20M12GE7K	22-20	0.32-0.52	1.18	2.2	4.8
RM16M23K	RC16M23K	RM16M23GE1K	RC16M23GE1K	RM16M23GE3K	RC16M23GE7K	20-16	0.50-1.50	1.80	3.2	7.1
RM14M50K	RC14M50K	-	-	-	-	16-14	1.5-2.5	2.05		
RM14M30K	RC14M30K	RM14M30GE1K	-	-	RC14M30GE7K	16-14	1.5-2.5	2.28		

Note : all dimensions are in mm

Tooling for machined contacts #16



Manual crimp pliers	Locator	Selector set-up - Wire section						Extraction tool
MH860 (M22520/7-01)	MH86164G or TP1142	6 0.5 mm ²	7 0.75 mm ²	7 1 mm ²	8 1.5 mm ²	-	RX2025GE1	
FT8	-	4 0.5 mm ²	4 0.75 mm ²	5 1 mm ²	5 1.5 mm ²	-		
AF8 (M22520/1-01)	TP1142	-	-	-	-	8 2.5 mm ²		

Following standard: EN 50306-2

Following standard: EN 50264-3-1

SOURIAU

souriau-industrial.com

contactindustry@souriau.com

Esterline
Connection Technologies